

[See all 22 Products in Family](#)

M37 x 0.75 Machine Vision Mounted Linear Glass Polarizing Filter



Stock #21-562 [CONTACT US](#)

1 [-](#) [+](#) MRP ₹9,887

● Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-9	₹9,887 each
Qty 10+	₹9,383 each
Need More?	Request Quote

Product Downloads

General

Mounted Imaging Filter **Type:**

Physical & Mechanical Properties

32.50 **Clear Aperture CA (mm):**

39.00 **Diameter (mm):**

Construction:

Optical Properties

Coating:
Hardcoated

Extinction Ratio:
up to 3000:1 @ ~600nm (nominal)

Surface Quality:
40-20

Wavelength Range (nm):
400 - 700

Threading & Mounting

Filter Thread:
M37 x 0.75

Mount Thickness Including Threads (mm):
9.6

Regulatory Compliance

Certificate of Conformance:
[View](#)

Reach 242:
[Compliant](#)

Country of Origin:
United States

Imported By:
Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Product Details

- Up to 3000:1 Extinction Ratio (nominal) @ ~600nm
- Mounted in a Rotating, Locking Housing
- 40-20 Surface Quality

Mounted Machine Vision Glass Linear Polarizers feature a rotatable threaded mount with a wide range of common machine vision threads from M22 to M105. A locking thumbscrew allows the polarizer to maintain its orientation in the event of vibrations or accidental movement in a system. In addition to polarizing incident unpolarized light, these linear polarizers can be used to greatly reduce specular glare and hot spots from reflective surfaces, smooth surfaces, or surfaces covered with grease, oil, or liquid. Mounted Machine Vision Glass Linear Polarizers are ideal for machine vision applications in manufacturing, industrial, and laboratory environments.