

[See all 7 Products in Family](#)

Mounted Window for 800nm, 0.80 NA, aplanoXX Aplan Objective

See More by [AdiOptica](#)



Mounted Window

Stock **#19-496** **1 In Stock**

⊖ 1 ⊕ ₹27,630

ADD TO CART

Volume Pricing	
Qty 1+	₹27,630 each
Need More?	Request Quote

Product Downloads

General

Model Number:
Window in Holder L9333.06 (+D12 800)

Type:
Mounted Window

Note:
Protective window for [#19-492](#)

Physical & Mechanical Properties

Length (mm):
4.40

8

Clear Aperture CA (mm):

Diameter (mm):

29.50

Optical Properties

Design Wavelength DWL (nm):

800

Wavelength Range (nm):

770 - 900

Damage Threshold, By Design:

25 mJ @ 5ns

Damage Threshold, Pulsed:

25 mJ @ 5ns

Regulatory Compliance

RoHS 2015:

Compliant

Certificate of Conformance:

[View](#)

Reach 250:

Compliant

Country of Origin:

Germany

Imported By:

Edmund Optics India Private Limited

Product Details

- Aplanatic Optical Design
- High Numerical Aperture for Small Spot Sizes
- Designs for 800 and 1030nm with Focusing Depth Up to 4mm
- [AdlOptica foXXus Multi-Focus Objectives](#) Also Available

AdlOptica aplanoXX Aplan Objectives compensate for spherical aberration and coma when focusing into glass, sapphire, silicon carbide, silicon, PMMA, and other transparent materials at depths up to 4mm. These objectives are designed to be used with ultrafast solid-state and fiber lasers and are optimized for 800nm (Ti:sapphire) and 1030nm (Yb:doped). Featuring C-Mount threading and an optical design insensitive to misalignment, these objectives are easy to integrate into laser systems. AdlOptica aplanoXX Aplan Objectives are ideal for micromachining glass, 3D nanofabrication, waveguide recording, and selective laser etching. A collar on the objective allows for manual adjustment of focus and a replaceable front window protects from debris during materials processing.

Technical Information

