

[See all 13 Products in Family](#)

M52 x 0.75 Mounted Linear Glass Polarizing Filter



Mounted Linear Glass Polarizing Filters

Stock **#25-086** **1 In Stock**

MRP ₹6,709

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-9	₹6,709 each
Qty 10-25	₹6,406 each
Need More?	Request Quote

Product Downloads

General

Mounted Imaging Filter **Type:**

Physical & Mechanical Properties

47.50 **Clear Aperture CA (mm):**

54.60 **Diameter (mm):**

Dichroic

Construction:

Optical Properties

Uncoated

Coating:

Approx. 19:1 at 400nm
Approx. 200:1 at 500nm
≥2700:1 at 550-650nm
Approx. 600:1 at 700nm

Extinction Ratio:

Float Glass

Substrate:

95% Efficiency

Polarization:

Single: 30
Crossed: 0.15

Transmission (%):

400 - 700

Wavelength Range (nm):

Threading & Mounting

M52 x 0.75

Filter Thread:

6.80

Mount Thickness (mm):

Environmental & Durability Factors

-15 to +70

Operating Temperature (°C):

Regulatory Compliance

[View](#)

Certificate of Conformance:

Japan

Country of Origin:

Imported By:
Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Product Details

- Stackable, Rotating Mount for Easy Integration into Imaging Systems
- Eliminate Hot Spots and Reduce Glare
- 95% Polarization Efficiency
- Also Available [Unmounted](#)

Mounted Linear Glass Polarizing Filters feature a rotatable threaded mount available in a wide range of standard thread sizes. Linear polarizing filters will transmit a single axis of polarization and can be used to reduce glare and hot spots in imaging systems. Two polarizing filters can be stacked to achieve a variable density effect. Thickness includes a 2mm male thread. Mounted Linear Glass Polarizing Filters have 95% polarization efficiency. The filters are also available [unmounted](#).

Technical Information

