

[See all 4 Products in Family](#)

## Multi-Grid Standard Stage Micrometer



Stock **#58-607** **8 In Stock**

- 1 + MRP ₹53,631

**i** Price inclusive of all taxes

**ADD TO CART**

Volume Pricing	
Qty 1-4	₹53,631 each
Qty 5+	₹51,061 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

### General

NIST Certification:  
No

### Physical & Mechanical Properties

Scale Divisions:  
0.5mm (25µm divisions), 1.0mm (50µm divisions),  
2.0mm (100µm divisions), 4.0mm (200µm  
divisions), angle grid (15° segments)

Dimensions (mm):  
25.4 x 76.2

---

1.50 ±0.100      **Thickness (mm):**

±0.100      **Dimensional Tolerance (mm):**

## Optical Properties

Chrome on Glass      **Substrate:**

60-40      **Surface Quality:**

---

## Regulatory Compliance

[Compliant](#)      **RoHS 2015:**

[View](#)      **Certificate of Conformance:**

[Compliant](#)      **Reach 235:**

---

United States      **Country of Origin:**

**Imported By:**  
Edmund Optics India Private Limited  
267, Greystone Building, Second Floor,  
6th Cross Rd, Binnamangala,  
Stage 1, Indiranagar, Bengaluru,  
Karnataka, India 560038  
Phone: +91- 80-6845 0000

---

## Product Details

- Calibrate Distortion in High Magnification Systems

The Multi-Grid Stage Micrometer features grids of varying frequency, and is ideal for calibrating distortion in microscopic systems. Grid sizes are 0.5mm (25µm divisions), 1.0mm (50µm divisions), 2.0mm (100µm divisions) and 4.0mm (200µm divisions). Mcrometer also features an angle grid (15° segments). Target is chrome on glass, 1" x 3" x 1.5mm.

---

;