

[See all 4 Products in Family](#)

Multi-Grid Standard Stage Micrometer w/ NIST Cert



Stock #59-275 **1 In Stock**

- 1 + MRP ₹1,01,421

Price inclusive of all taxes

ADD TO CART

| Volume Pricing | |
|----------------|-------------------------------|
| Qty 1-4 | ₹1,01,421 each |
| Qty 5+ | ₹96,387 each |
| Need More? | Request Quote |

Product Downloads

General

NIST Certification:
Yes

Physical & Mechanical Properties

Scale Divisions:
0.5mm (25µm divisions), 1.0mm (50µm divisions),
2.0mm (100µm divisions), 4.0mm (200µm
divisions), angle grid (15° segments)

Dimensions (mm):
25.4 x 76.2

1.50 ±0.100 **Thickness (mm):**

±0.100 **Dimensional Tolerance (mm):**

Optical Properties

Chrome on Glass **Substrate:**

60-40 **Surface Quality:**

Regulatory Compliance

Compliant **RoHS 2015:**

View **Certificate of Conformance:**

Compliant **Reach 235:**

United States **Country of Origin:**

Imported By:
Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Product Details

- Calibrate Distortion in High Magnification Systems

The Multi-Grid Stage Micrometer features grids of varying frequency, and is ideal for calibrating distortion in microscopic systems. Grid sizes are 0.5mm (25µm divisions), 1.0mm (50µm divisions), 2.0mm (100µm divisions) and 4.0mm (200µm divisions). Mcrometer also features an angle grid (15° segments). Target is chrome on glass, 1" x 3" x 1.5mm.

;