

Nikon Type N 8ml PCB Free Immersion Oil

See More by [Nikon](#)



Stock **#75-380** NEW [CONTACT US](#)

-

1

+

₹1,044

ADD TO CART

Volume Pricing	
Qty 1+	₹1,044 each
Need More?	Request Quote

Product Downloads

General

	Manufacturer:
Nikon	

Optical Properties

	Index of Refraction (n _d):
1.518	
	Abbe Number (v _d):
41	

Environmental & Durability Factors

	Operating Temperature (°C):
23	

Regulatory Compliance


Certificate of Conformance:	
View	
Country of Origin:	
Japan	
Imported By:	
Edmund Optics India Private Limited	

Product Details

• Superior UV Transmission
• High Numerical Aperture Designs
• Feature Low Auto-Fluorescence Materials

Nikon CFI Super Fluor Objectives are designed to provide superior transmission to ultraviolet applications operating down to 340nm, including for use with fluorochromes indo-1, fura-2, and fluo-3, or for photo-activation of caged compounds. Nikon CFI Super Fluor Objectives are designed using low auto-fluorescence materials along with high numerical apertures to guarantee sharp, bright fluorescence images. These microscope objectives have been optimized for improved signal-to-noise ratios at short wavelengths.

Technical Information



Dimensions (mm)						
Stock No.	Magnification	Parafoval Length	A	B	C	D
#88-374	4X	60.06	30.0	44.4	19.7	M25 x0
#88-375	10X	60.06	32.0	58.7	8.0	M25 x0
#88-376	20X	60.06	33.5	58.9	9.0	M25 x0
#88-377	40X	60.06	33.0	59.6	7.5	M25 x0