


Micro Line and Dot Micrometer on Opal Glass w/ NIST Cert



Stock **#59-274** [CONTACT US](#)

-

1

+

₹1,18,350

ADD TO CART

Volume Pricing	
Qty 1-4	₹1,18,350 each
Qty 5+	₹1,12,527 each
Need More?	Request Quote

Product Downloads

SPECIFICATIONS

General

Yes

NIST Certification:

Physical & Mechanical Properties

Scale Divisions:

2µm, 3µm, 4µm, 5µm, 6µm, 7µm, 8µm, 9µm, 10µm, 25µm, 50µm, 75µm, 100µm	
25.4 x 76.2	Dimensions (mm):
1.50 ±0.100	Thickness (mm):
±0.100	Dimensional Tolerance (mm):

Optical Properties

Chrome on Opal Glass	Substrate:
----------------------	------------

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 235:

PRODUCT DETAILS

- New Opal Version Available
- Calibrate Pixel Dithering
- Lines and Dot Range from 2µm to 100µm

The Micro Line and Dot Standard is designed to calibrate imaging devices performing critical measurements. The pattern features known dot and line sizes of 2µm, 3µm, 4µm, 5µm, 6µm, 7µm, 8µm, 9µm, 10µm, 25µm, 50µm, 75µm, 100µm. Calibrating with this target can limit the effects of pixel dithering in image processing algorithms. Target is chrome on glass or chrome on opal.