


[See all 4 Products in Family](#)

Micro Line and Dot Standard Stage Micrometer w/ NIST Cert



Stock #59-273 **4 In Stock**

- 1 + MRP ₹1,23,192

i Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-4	₹1,23,192 each
Qty 5+	₹1,17,128 each
Need More?	Request Quote

Product Downloads

General

Yes **NIST Certification:**

Physical & Mechanical Properties

Scale Divisions:
2µm, 3µm, 4µm, 5µm, 6µm, 7µm, 8µm, 9µm, 10µm,
25µm, 50µm, 75µm, 100µm

Dimensions (mm):
25.4 x 76.2

Thickness (mm):

1.50 ±0.100

Dimensional Tolerance (mm):

±0.100

Optical Properties

Chrome on Glass

Substrate: □

60-40

Surface Quality:

Regulatory Compliance

RoHS 2015:

[Compliant](#)

Certificate of Conformance:

[View](#)

Reach 235:

[Compliant](#)

Country of Origin:

United States

Imported By:

Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Product Details

- New Opal Version Available
- Calibrate Pixel Dithering
- Lines and Dot Range from 2µm to 100µm

The Micro Line and Dot Standard is designed to calibrate imaging devices performing critical measurements. The pattern features known dot and line sizes of 2µm, 3µm, 4µm, 5µm, 6µm, 7µm, 8µm, 9µm, 10µm, 25µm, 50µm, 75µm, 100µm. Calibrating with this target can limit the effects of pixel dithering in image processing algorithms. Target is chrome on glass or chrome on opal.