

Microlens Array 10 x 10mm, 300μm Pitch, 1° Divergence, NIR II Coated



Microlens Arrays



Stock #21-149 10 TO 12 DAYS

-

1

+

₹70,035.00

ADD TO CART

Qty 1-10	₹70,035.00
Qty 11+	₹62,988.00
Volume Pricing	Request Quote

Get Product Downloads

Effective Focal Length EFL (mm):
8.70

Substrate: [Fused Silica](#)

Coating:

NIR II (750-1550nm)
Type: Lens Array
Wavelength Range (nm): 750 - 1550
Coating Specification: R _{abs} ≤1.5% @ 750 - 800nm R _{abs} ≤1.0% @ 800 - 1550nm R _{avg} ≤0.7% @ 750 - 1550nm
Dimensional Tolerance (mm): ±0.05
Dimensions (mm): 10.0 x 10.0
Divergence Angle (°): ±1
Lens Profile: Spherical
Pitch (μm): 300.00
Pitch Tolerance (μm): ±0.25
Radius R (mm): 4.00
Thickness (mm): 1.20
Thickness Tolerance (mm): ±0.05
Type of Optics: Plano-Convex

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant