

## Norland Optical Adhesive NOA 139, 1 oz. Application Bottle

See More by [Norland](#)



Norland Optical Adhesive NOA 139, 1 oz. Application Bottle, #15-696

Stock **#15-696** **2 In Stock**

⊖ 1 ⊕ ₹15,660

**ADD TO CART**

Volume Pricing	
Qty 1-4	₹15,660 each
Qty 5+	₹15,138 each
Need More?	<a href="#">Request Quote</a>

Product Downloads

### SPECIFICATIONS

#### General

Size (oz):

1

Norland Number:

139

4 months **Shelf Life:**

Bottle **Type:**

Low viscosity adhesive for bonding glass or plastic. **Typical Applications:**

### Optical Properties

1.39 @589nm **Index of Refraction (n<sub>d</sub>):**

315 - 450 **Absorption Range (nm):**

### Material Properties

Excellent **Glass Bonding:**

Good **Metal Bonding:**

Good **Plastic Bonding:**

865 **Viscosity (cps):**

Glass to Glass **Bonding Type:**

6 **Energy for Full Cure (J/cm<sup>2</sup>):**

### Environmental & Durability Factors

Flexible **Durability:**

### Regulatory Compliance

[Compliant](#) **RoHS 2015:**

[View](#) **Certificate of Conformance:**

[Compliant](#) **Reach 251:**

## PRODUCT DETAILS

- Excellent Optical Qualities
- Adhesives for Glass, Metal, and Plastic Bonding
- Cure Quickly when Exposed to UV Light
- [Preloaded Norland Optical Adhesive Syringes](#) Also Available

Norland Optical Adhesives are clear, solvent-free optical adhesives designed to fully cure in only minutes when exposed to ultraviolet light. These adhesives are used in precision alignment or positioning applications that require a robust and resilient bond. Norland Optical Adhesives feature a variety of bonding types, including but not limited to glass to glass, glass to glass/metal, and plastic to plastic/glass. To use Norland Optical Adhesives, apply the adhesive to the optical surface, position the components, and use a [UV light source](#) to set the components in place. Since the adhesive will not cure until exposed to UV light, time can be taken during the positioning process to perfect product alignment.

## TECHNICAL INFORMATION

NORLAND OPTICAL ADHESIVES (NOA) APPLICATION NOTES	
Title	Description
<a href="#">Applying Adhesive</a>	Covers best practices to use when applying Norland Optical Adhesives to ensure an even adhesive layer while avoiding air bubbles.
<a href="#">Chemical Resistance of NOA</a>	Covers the effects of various chemicals on Norland Optical Adhesives including acids, bases, and solvents.
<a href="#">Preventing Lens Separations with NOA</a>	Covers best practices to avoid adhesive failures when bonding optical elements.
<a href="#">Separating Lenses Bonded with NOA</a>	Covers how to unbond optical elements bonded with Norland Optical Adhesives.