


Normal Response, 0.20mm², Silicon Detector



Silicon Photodiodes

Stock **#57-506** 10 TO 12 DAYS



1



₹3,219.00

ADD TO CART

Qty 1-4

₹3,219.00

Qty 5+

₹2,871.00

Volume Pricing

[Request Quote](#)

Get Product Downloads

Operating Temperature (°C):
-40 to 100

Type:
Biased

Typical Applications:
High light levels, pulse detectors, AC light measurement

Terminal Capacitance (pF): 4 @ 0 V; 1 @ 10 V
Rise Time (ns): 6 @ -10 V/50 Ω, 632nm
Voltage Bias, V_{Bias} (V): -10
Responsivity @ 970nm (AW): 0.65
Active Area (mm²): 0.20
Noise Equivalent Power NEP (W/ Hz^{1/2}): 2.8 x 10 ⁻¹⁵
Detectivity (cmHz^{1/2}/W): 1.6 x 10 ¹³ @ -10 V, 970nm
Maximum Breakdown Voltage (V): 30.00
Model Number: PIN-020A
Note: Normal Response
Construction: PIN
Dark Current I_d (nA): 0.01 @ 10V
Protective Window: Borosilicate
Package: TO-18

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View