

TECHSPEC[®] C-Mount, 35mm Sq. x 3mm Thick Plate Mount



Mount Only (no optics included) for any 35mm sq x 3mm Thick Plate, #56-265

Stock **#56-265** **6 In Stock**

-

1

+

₹19,438

ADD TO CART

Volume Pricing	
Qty 1-4	₹19,438 each
Qty 5-9	₹17,149 each
Qty 10-25	₹15,785 each
Need More?	Request Quote

Product Downloads

General	
Optic Mount (Fixed)	Function:
Square	Type of Optics:
Note:	
Includes one C-Mount Aperture Cap (#55-245)	
Dimensions of Compatible Optics (mm):	
35.0 Sq.	

Physical & Mechanical Properties

38.0 x 38.8 x 50.0	Dimensions (mm):
38.0	Extension Length (mm):
3.00	Min. Thickness of Compatible Optics (mm):
6.00	Max. Thickness of Compatible Optics (mm):

Threading & Mounting

C-Mount	Thread Type:
1/4-20	Compatible Post:

Regulatory Compliance

View	Certificate of Conformance:
United States	Country of Origin:
Edmund Optics India Private Limited	Imported By:

Product Details

- C, S, and T-Mount Solutions for Mounting Cube and Plate Beamsplitters, Filters, and Mirrors
- Provides a 90° Mounting Interface
- 1/4-20 and M6 Tapped Mounting Threads for English or Metric Based Systems

TECHSPEC® C, S, and T-Mount Cube and Plate Mounts allow for the integration of cube and plate optics into C, S, and T-Mount systems. These mounts feature four C, S, or T-Mount threaded apertures that can also act as connection points for other C, S, or T-Mount components. Either an M6 or 1/4-20 tapped hole is provided on the base for post mounting, making these mounts compatible with breadboard and benchtop systems. TECHSPEC C, S, and T-Mount Cube and Plate Mounts provide a 90° mounting interface ideal for placing beamsplitters, filters, and mirrors within a system. C, S, and T-Mount Aperture Caps are available to block light from unused openings and to protect the optic from dust and debris.

Note: [#11-139](#) and [#11-142](#) each include one S-Mount Aperture Cap ([#11-137](#))

Technical Information

