

Ocean Optics HR2 NIR High Resolution Spectrometer

See More by [Ocean Optics](#)



Stock **#90-024** NEW **1 In Stock**

-

1

+

₹4,85,069

 Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1+	₹4,85,069 each
Need More?	Request Quote

Product Downloads

General	
OceanDirect & OceanView	
Software:	
1µs - 2s	
Integration Time:	
HR-2N750-25	
Model Number:	
Includes manual QR code, software QR code, calibration reports for wavelength and linearity, 1 m USB cable	
Note:	

SMA905	Input Port Termination:
Ruled Diffraction Grating: 1200 Grooves/mm, Blazed @ 750nm	Grating:
Cross Czerny Turner	Optical Bench:
Physical & Mechanical Properties	
25	Slit Width (µm):
0.9306	Weight (kg):
149.0 x 106.4 x 48.2	Dimensions (mm):
Optical Properties	
0.24	Spectral Resolution (nm):
750 - 900	Wavelength Range (nm):
Sensor	
CCD	Type of Sensor:
Electrical	
Signal to Noise S/N Ratio:	
Single Scan @ 10 ms: 380:1	
Max per second with High Speed Averaging Mode:	
25,800:1	
Hardware & Interface Connectivity	
USB, RS-232	Computer Interface:
Threading & Mounting	
(3) 2-56	Mounting Threads:
Environmental & Durability Factors	
0 to +55	Operating Temperature (°C):
-30 to +70	Storage Temperature (°C):
0.02 nm/°C	Thermal Stability:
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 250:
United States	Country of Origin:
Imported By:	
Edmund Optics India Private Limited	
267, Greystone Building, Second Floor,	
6th Cross Rd, Binnamangala,	
Stage 1, Indiranagar, Bengaluru,	
Karnataka, India 560038	
Phone: +91- 80-6845 0000	

Product Details

- High Resolution Spectrometers for Narrow Peak Identification
- Spectral Ranges Spanning UV-VIS, VIS-NIR, and NIR Wavelengths
- Rapid Acquisition Speed and Excellent Thermal Stability

Ocean Optics HR High Resolution Spectrometers, available in HR2, HR4, and HR6 models, are designed to identify narrow spectral peaks with detailed spectral analysis for applications that require high-resolution solutions. The HR2 spectrometers feature high-resolution performance, fast scan speeds, and excellent thermal stability, providing rapid, real-time results ideal for applications such as plasma monitoring and pharmaceutical analysis. The HR4 spectrometers combine high-resolution spectral analysis with excellent thermal stability, making these models excel in precision-demanding environments such as DNA/RNA analysis, biomedical research, and high-throughput reflection testing. The HR6 spectrometers offer high sensitivity, high resolution, and excellent signal-to-noise ratio (SNR) performance for applications including protein absorbance and emission of broadband sources. The Ocean Optics HR High Resolution Spectrometers include the user-friendly OceanView software system to optimize spectrometer performance, ease system integration, and access data for analysis.

