

## Mounted M58 x 0.75 Threaded - Blue Filter



Stock #54-777 CLEARANCE **1 In Stock**

₹3,563

ADD TO CART

Volume Pricing	
Qty 1+	₹3,563 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

### General

AR Coating: MgF<sub>2</sub>

**Note:**

Mounted Imaging Filter

**Type:**

Hoya B-440 or equivalent

**Type of Filter:**

### Physical & Mechanical Properties

54.0

**Clear Aperture CA (mm):**

**Outer Diameter (mm):**

60.0

2.5

5.00

Substrate Thickness (mm):

Thickness with Mount (mm):

### Optical Properties

Blue **Color:**

480.00 **Cut-Off Wavelength (nm):**

395.00 **Cut-On Wavelength (nm):**

B-440 **Glass/Filter Number:**

1.55 **Index of Refraction (n<sub>d</sub>):**

Colored Glass **Substrate:**

80-50 **Surface Quality:**

400 - 700 **Wavelength Range (nm):**

### Threading & Mounting

M58 x0.75 **Filter Thread:**

2.5 **Thickness of Compatible Optics (mm):**

### Regulatory Compliance

Compliant **RoHS 2015:**

View **Certificate of Conformance:**

Japan **Country of Origin:**

Edmund Optics India Private Limited **Imported By:**

## Product Details

- Improve Contrast
- Isolate Spectral Regions/Colors
- Precision Colored Glass

Mounted Color Filters are ideal for machine vision and are best used with black-and-white cameras to yield increased contrast and resolution. Utilizing the principle "Like Colors Lighten Like Colors" will maximize results. Daylight Blue filters increase color temperature from 3300K to 5500K (daylight). Color camera settings (Red/Blue gain level and AWC) yield further optimization when used in conjunction with lamp selection (quartz-halogen and fluorescent). Mounted Color Filters provide wide fields of view unobtainable with angle-sensitive filters.

All filters can be threaded together via identical male and female threads on each mount. Color filters can also be used in conjunction with [mounted UV filters](#) to block unwanted ultraviolet light and protect the filters in extreme environments.

## Technical Information

