

Olympus LUCPLFLN40X2 40X Objective

See More by [Olympus](#)



Stock #90-477 NEW 1 In Stock

-

1

+

₹2,52,300

ADD TO CART

Volume Pricing	
Qty 1+	₹2,52,300 each
Need More?	Request Quote

Product Downloads

General	
Model Number:	
LUCPLFLN40X2	
Compatible Tube Lens Focal Length (mm):	
Focal Length: 180mm	
Type:	
Microscope Objective	
Style:	
Infinity Corrected	
Manufacturer:	
Olympus	

Physical & Mechanical Properties	
0.66	Field of View (mm):
40.94	Length excluding Threads (mm):
29.00	Maximum Diameter (mm):
140	Weight (g):

Optical Properties	
0.00 - 2.00	Compatible Cover Glass Thickness (mm):
4.50	Focal Length FL (mm):
40X	Magnification:
0.60	Numerical Aperture NA:
0.56	Resolving Power (μm):
0.76	Depth of Field (μm):
2.70 - 4.00	Working Distance (mm):
340 - 1300	Wavelength Range (nm):
26.5	Field Number (mm):
45	Parfocal Length (mm):
N/A	Immersion Liquid:

Threading & Mounting	
RMS / 20.32mm x 36 TPI	Mounting Threads:

Regulatory Compliance	
Exempt	RoHS 2015:
View	Certificate of Conformance:
Contains SVHC(s)	Reach 247:
Japan	Country of Origin:
Edmund Optics India Private Limited	Imported By:

Product Details

- Long Working Distances to Image Through Dishes, Bottles, or Slides
- Correction Collars to Precisely Adjust Working Distance
- Ideal for Inverted Microscope Configurations

Olympus Long Working Distance Plan Semi Apochromatic Objectives are designed for long working distances to image samples through dishes, bottles, slides, or other vessels. These objectives feature correction collars to precisely adjust the working distance based on thickness of the vessel to obtain clear specimen images. They offer a large field number of 26.5, transmission from the UV to the NIR, and correct for chromatic aberration at blue, green and red wavelengths. Olympus Long Working Distance Plan Semi Apochromatic Objectives are ideal for use with inverted microscope configurations, including standard microscopes or custom inverted setups.