

# Nikon 200mm Large FOV Tube Lens

See More by [Nikon](#)



Stock #75-379 **NEW** 1 In Stock

1 MRP ₹1,42,308

Price inclusive of all taxes

**ADD TO CART**

### Volume Pricing

Qty 1+	₹1,42,308 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

### General

Tube Lens	Type:
Nikon	Manufacturer:

### Physical & Mechanical Properties

27.00	Length (mm):
43	Maximum Diameter (mm):

## Optical Properties

200.00	Focal Length FL (mm):
1x	Magnification:
380 - 1000	Wavelength Range (nm):
25	Field Number (mm):
42	Entrance Pupil Diameter (mm):

## Threading & Mounting

M43x0.5	Mounting Threads:
---------	-------------------

## Regulatory Compliance

<a href="#">View</a>	Certificate of Conformance:
Japan	Country of Origin:
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	Imported By:

## Product Details

- Superior UV Transmission
- High Numerical Aperture Designs
- Feature Low Auto-Fluorescence Materials

Nikon CFI Super Fluor Objectives are designed to provide superior transmission to ultraviolet applications operating down to 340nm, including for use with fluorochromes indo-1, fura-2, and fluo-3, or for photo-activation of caged compounds. Nikon CFI Super Fluor Objectives are designed using low auto-fluorescence materials along with high numerical apertures to guarantee sharp, bright fluorescence images. These microscope objectives have been optimized for improved signal-to-noise ratios at short wavelengths.

## Technical Information

Stock No.	Magnification	Parfocal Length	Dimensions (mm)			
			A	B	C	D
#75-345	4X	60.06	30.0	44.3	19.7	M25 x 0.75
#88-375	10X	60.06	32.0	58.9	12.0	M25 x 0.75
#88-376	20X	59.90	33.5	58.9	9.0	M25 x 0.75
#75-346	40X	60.06	32.0	59.8	8.3	M25 x 0.75

