

[See all 5 Products in Family](#)

Olympus MPLN 50X Objective

See More by [Olympus](#)



Stock #87-138 NEW 1 In Stock

-

1

+

₹1,02,225

ADD TO CART

Volume Pricing	
Qty 1+	₹1,02,225 each
Need More?	Request Quote

Product Downloads

General	
1-U2M230	Model Number:
Compatible Tube Lens Focal Length (mm): Focal Length: 180mm	
Microscope Objective	Type:
Infinity Corrected	Style:
Olympus	Manufacturer:

Physical & Mechanical Properties	
0.44	Field of View (mm):
44.62	Length excluding Threads (mm):
24	Maximum Diameter (mm):
113	Weight (g):

Optical Properties	
N/A	Compatible Cover Glass Thickness (mm):
3.60	Focal Length FL (mm):
50X	Magnification:
0.75	Numerical Aperture NA:
0.45	Resolving Power (μm):
0.49	Depth of Field (μm):
0.38	Working Distance (mm):
400 - 700	Wavelength Range (nm):
22	Field Number (mm):
45	Parfocal Length (mm):
N/A	Immersion Liquid:

Threading & Mounting	
RMS / 20.32mm x 36 TPI	Mounting Threads:

Regulatory Compliance	
View	Certificate of Conformance:
Japan	Country of Origin:
Edmund Optics India Private Limited	Imported By:

Product Details

- Ideal for Transmitted or Reflected Brightfield Microscopy
- Produce Flat Images Up to Field Number (F.N.) 22
- Excellent Price-to-Performance Ratio
- Additional [Olympus Infinity Corrected Objectives](#) Available

Olympus MPlan Achromatic Objectives are designed for brightfield observations, providing excellent contrast and optimum flatness throughout the field of view. Engineered for inspection of silicon wafers, metals, and other industrial microscopy applications, these objectives may also be used in Raman microscopes and other reflected light techniques without coverslip correction. Olympus MPlan Achromatic Objectives are available in 5X-100X magnifications and provide excellent image flatness up to F.N. 22. [Olympus Plan Achromatic Objectives](#) are also available for observing biological specimens.