

[See all 1 Products in Family](#)

NIST Traceable Color Transmission Calibration Slide



NIST Traceable Color Transmission Calibration Slides

Stock **#37-541** **4 In Stock**

-

1

+

₹1,71,513

 Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-4	₹1,71,513 each
Qty 5+	₹1,62,964 each
Need More?	Request Quote

Product Downloads

General	
Note: Includes Calibration Certificate, Calibration Data Report, Conversion Spreadsheet, USB Flash Drive with Data and Spreadsheet, and Protective Case	
24	Number of Colors:
Yes	NIST Certification:

Physical & Mechanical Properties	
75.00	Length (mm):
25.00	Width (mm):
9	Number of Patches:
150, 650, 1150, 1650, 2150, 2650, 3150, 3650, 4150	Size of Patches (µm):
Electrical	
Negative	Polarity:
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 235:
United States	Country of Origin:
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	Imported By:

Product Details

- 24 Calibrated Colors Patches
- 9 Patch Diameters from 150 to 4150µm
- Compatible with Oil Immersion Objectives

NIST Traceable Color Transmission Calibration Slides are used to assess and calibrate the color accuracy of microscopy measurement systems. These slides feature 24 large color patches with diameters from 4150µm, calibrated for spectral transmission, down to 150µm. NIST traceable calibration data is included for these serialized and calibrated slides to facilitate accurate conversion of the color patches to other color spaces of interest such as Adobe RGB 1998, CIE L*A*B* and XYZ. These NIST Traceable Color Transmission Calibration Slides include a calibration certificate, a calibration data report, a conversion spreadsheet, a USB flash drive with electronic calibration information, and a protective storage case. A protective glass cover over the color film minimizes deterioration of the calibrated color patches and also allows for compatibility with oil immersion objectives.