

[See all 48 Products in Family](#)

# Norland Optical Adhesive NOA 65, 1 lb. Bottle

See More by [Norland](#)



Norland Optical Adhesive NOA65, 1 lb. Bottle

Stock **#16-779** **8 In Stock**

MRP ₹34,409

**1** Price inclusive of all taxes

**ADD TO CART**

Volume Pricing	
Qty 1-4	₹34,409 each
Qty 5-11	₹30,968 each
Qty 12+	₹29,428 each
Need More?	<a href="#">Request Quote</a>

## Product Downloads

## General

16 **Size (oz):**

65 **Norland Number:**

4 months **Shelf Life:**

Bottle **Type:**

**Typical Applications:**  
More flexible adhesive for extra low strain applications. Suitable for cold blocking applications.

UV **Cure:**

## Optical Properties

1.52 @ 589nm **Index of Refraction ( $n_d$ ):**

350 - 380 **Absorption Range (nm):**

## Material Properties

Good **Glass Bonding:**

Good **Metal Bonding:**

Fair **Plastic Bonding:**

1200 **Viscosity (cps):**

Glass to Glass/Metal **Bonding Type:**

4.5 **Energy for Full Cure ( $J/cm^2$ ):**

## Environmental & Durability Factors

Flexible **Durability:**

## Regulatory Compliance

[Compliant](#) **RoHS 2015:**

[View](#) **Certificate of Conformance:**

[Compliant](#) **Reach 251:**

United States **Country of Origin:**

**Imported By:**  
Edmund Optics India Private Limited  
267, Greystone Building, Second Floor,  
6th Cross Rd, Binnamangala,  
Stage 1, Indiranagar, Bengaluru,  
Karnataka, India 560038  
Phone: +91- 80-6845 0000

## Product Details

- Excellent Optical Qualities
- Adhesives for Glass, Metal, and Plastic Bonding
- Cure Quickly when Exposed to UV Light
- [Preloaded Norland Optical Adhesive Syringes](#) Also Available

Norland Optical Adhesives are clear, solvent-free optical adhesives designed to fully cure in only minutes when exposed to ultraviolet light. These adhesives are used in precision alignment or positioning applications that require a robust and resilient bond. Norland Optical Adhesives feature a variety of bonding types, including but not limited to glass to glass, glass to glass/metal, and plastic to plastic/glass. To use Norland Optical Adhesives, apply the adhesive to the optical surface, position the components, and use a [UV light source](#) to set the components in place. Since the adhesive will not cure until exposed to UV light, time can be taken during the positioning process to perfect product alignment.

## Technical Information

**NORLAND OPTICAL ADHESIVES (NOA) APPLICATION NOTES**

Title	Description
<a href="#">Applying Adhesive</a>	Covers best practices to use when applying Norland Optical Adhesives to ensure an even adhesive layer while avoiding air bubbles.
<a href="#">Chemical Resistance of NOA</a>	Covers the effects of various chemicals on Norland Optical Adhesives including acids, bases, and solvents.
<a href="#">Preventing Lens Separations with NOA</a>	Covers best practices to avoid adhesive failures when bonding optical elements.
<a href="#">Separating Lenses Bonded with NOA</a>	Covers how to unbond optical elements bonded with Norland Optical Adhesives.