

[See all 21 Products in Family](#)

Oryx® ORX-10G-310S9M Mono 10GigE

See More by [Teledyne FLIR](#)



ORYX-10G-310S9C



Stock #20-254 **1 In Stock**

- 1 + MRP ₹7,52,958

Price inclusive of all taxes

ADD TO CART

Volume Pricing

Qty 1+	₹7,52,958 each
--------	----------------

Volume Pricing

Need More?

[Request Quote](#)

Note: This item requires accessories for use | [Learn More](#)

Product Downloads

Monochrome

Spectrum:

General

Monochrome Camera

Type:

ORX-10G-310S9M

Model Number:

FLIR

Manufacturer:

Oryx®

Camera Series:

Physical & Mechanical Properties

60 x 60 x 115

Dimensions (mm):

508

Weight (g):

Full

Housing:

Sensor

240MB

Image Buffer:

APS-C

Sensor Format:

31.00

Resolution (Megapixels):

26.00

Frame Rate (fps):

6,464 x 4,852

Pixels (H x V):

3.45 x 3.45

Pixel Size, H x V (µm):

22.30 x 16.74

Sensing Area, H x V (mm):

Sony IMX342

Imaging Sensor:

Progressive Scan CMOS

Type of Sensor:

Global

Shutter Type:

8/10/12 Bit

Pixel Depth:

39µs - 30s

Exposure Time:

67.17

Dynamic Range (dB):

GigE Vision

Machine Vision Standard:

Electrical

13.9

Power Consumption (W):

Hardware & Interface Connectivity

10GigE

Interface:

GigE interface with Screw Locks

Connector:

Power Supply:

Power Supply Required and Sold Separately.

USA: [#19-803](#)

Europe: [#19-803](#)

Japan: [#19-803](#)

Korea: Not Available

China: [#19-803](#)

GPIOs:
1 opto-isolated input, 1 opto-isolated output, 2 non-isolated bi-directional

Synchronization:
Hardware Trigger (GPIO) or Software Trigger

Interface Port Orientation:
Back Panel

GPIO Connector Type:
12-pin Hirose (HR10)

Threading & Mounting

Mount:
F-Mount (With [#20-256](#))

Mounting Threads:
Built-in 1/4-20 Tripod Mount Adapter

Environmental & Durability Factors

Operating Temperature (°C):
0 to +50

Storage Temperature (°C):
-30 to +60

Regulatory Compliance

Certificate of Conformance:
[View](#)

Country of Origin:
Canada

Imported By:
Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91-80-6845 0000

Product Details

- 10GBASE-T (10GigE) Ethernet Interface
- 3.2 to 31 Megapixel Sony 4th Gen Pregius S Sensors
- Supports 4K60, 12-bit System Integration
- Tripod Adapter Built into Larger Oryx® Models



Teledyne
Authorized
Distributor

Teledyne FLIR IIS Oryx 10GigE: High throughput, Award-winning camera designs

Reliably capture images at high speed

The **Oryx 10GigE** camera family supports transfer speeds of up to 10 Gbit/s enabling capture of 4K resolution, 12-bit images at speeds exceeding 60 FPS. Reliable image transfer at high bandwidth is further improved with Myricom bundles and packet resend feature. A range of sensor options offer resolutions from 3.2 Megapixel up to 31 Megapixel. Oryx features include IEEE1588 clock synchronization and full compatibility with several popular third-party software supporting GigE Vision. Oryx's 10GBASE-T interface is a proven and widely deployed standard that provides reliable image transfer at cable lengths over 50 meters on inexpensive CAT6A, and up to 30 meters on CAT5e.

Note: The ORX-10G-310S9 and ORX-10G-245S8 cameras require an F-Mount lens adapter (sold separately).

Features

- Color or monochrome sensors
- Various frame triggering options including up to 8 sets of 2-feature sequencer
- Pixel binning, decimation, ROI
- On camera image processing includes Gamma, LUT, and sharpness

Applications

- Stadium venues
- Site security
- Factory automation
- Traffic monitoring
- Inspection systems