

# Coherent® OBIS™ FP 1193831 | 488nm LX 30mW Laser, Fiber Pigtail, FC

See More by [Coherent®](#)



Coherent® High Performance OBIS™ Fiber-Pigtailed Laser Systems



Stock #88-031 [CONTACT US](#)

- 1 + MRP ₹8,66,592

Price inclusive of all taxes

**ADD TO CART**

Volume Pricing	
Qty 1+	₹8,66,592 each
Need More?	<a href="#">Request Quote</a>

Product Downloads



**General**

Warm-Up Time (minutes):  
<5

Fiber Cable Type:  
3mm Mono-Coil

Manufacturer:  
Coherent®

Diode	<b>Type of Laser:</b>
IIIb	<b>Laser Class - CDRH:</b>
1193831	<b>Model Number:</b>

## Optical Properties

100:1	<b>Polarization:</b>
TEM <sub>00</sub>	<b>Spatial Mode:</b>
488.00 ±5	<b>Wavelength (nm):</b>
≤1.1	<b>Mode Quality, M<sup>2</sup>:</b>
Blue	<b>Color:</b>
0.05	<b>Fiber Numerical Aperture NA (1/e<sup>2</sup>):</b>

## Electrical

30	<b>Output Power (mW):</b>
<2	<b>Power Stability (%):</b>
Digital: 150	<b>Modulation Frequency (MHz):</b>
Analog: 500	<b>Modulation Frequency (kHz):</b>
≤0.2% (20Hz to 20MHz)	<b>RMS Noise:</b>

## Hardware & Interface Connectivity

Power Supply Required and Sold Separately. USA: <a href="#">#87-473</a> Europe: <a href="#">#87-473</a> Japan: <a href="#">#87-473</a> Korea: <a href="#">#87-473</a> China: <a href="#">#87-473</a>	<b>Power Supply:</b>
FC/APC; 8° angled	<b>Output from Fiber:</b>
Fiber-Coupled	<b>Output Type:</b>

## Environmental & Durability Factors

10 to 50	<b>Operating Temperature (°C):</b>
----------	------------------------------------

## Regulatory Compliance

<a href="#">Compliant</a>	<b>RoHS 2015:</b>
<a href="#">View</a>	<b>Certificate of Conformance:</b>
Singapore	<b>Country of Origin:</b>
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	<b>Imported By:</b>

## Product Details

A power supply is required for operation and sold separately. OBIS remote is required for CDRH certified systems. The OBIS heat sink is recommended.

- High Performance OBIS™ LX/LS Lasers with Added Fiber Optic Capability
- Permanent Fiber Attachment Extends Lifetime with Guaranteed Power
- Single-Mode Polarization-Maintaining Fiber with an FC/APC Connector Provide High-Quality and Low-Noise Laser Beam Output
- [Coherent® High Performance OBIS™ LX/LS Laser Systems](#) Also Available

Coherent® High Performance OBIS™ LX/LS Fiber-Pigtailed Laser Systems are plug-and-play lasers available in wavelengths from the ultraviolet to the near-infrared with an added fiber attachment. The fiber optic is permanently attached to the laser, providing an extended lifetime of the fiber and guaranteed power consistency. An FC/APC connector terminates the fiber to enable connections to other systems without concern for high noise interference. Coherent® High Performance OBIS™ LX/LS Fiber-Pigtailed Laser Systems produce high-quality, low-noise laser beams and also allow for hands-free operation. These fiber-pigtailed lasers are used in confocal microscopy, DNA sequencing, polymerase chain reaction (PCR) diagnostic instruments, flow cytometry, medical imaging, and instrumentation applications.

This downloadable PDF provides guidance on interfacing with OBIS controllers and power supplies, mounting and connecting the heatsink, and starting modulation.

[Download Startup Guide](#)

---