

Ocean Optics HR6 VIS-NIR High Resolution Spectrometer

See More by [Ocean Optics](#)



Stock **#90-029** NEW CONTACT US

-

1

+

₹6,48,585

ADD TO CART

Volume Pricing	
Qty 1+	₹6,48,585 each
Need More?	Request Quote

Product Downloads

General	
Software:	
OceanDirect & OceanView	
Integration Time:	
7.2 ms – 5 s	
Model Number:	
HR-6VIS500-25	
Note:	
Includes manual QR code, software QR code, calibration reports for wavelength and linearity, 1 m USB cable	

SMA905	Input Port Termination:
Ruled Diffraction Grating: 600 Grooves/mm, Blazed @ 500nm	Grating:

Cross Czerny Turner	Optical Bench:
---------------------	----------------

Physical & Mechanical Properties

25	Slit Width (µm):
0.9306	Weight (kg):

149.0 x 106.4 x 48.2	Dimensions (mm):
----------------------	------------------

Optical Properties

0.57	Spectral Resolution (nm):
400 - 840	Wavelength Range (nm):

Sensor

CCD	Type of Sensor:
-----	-----------------

Electrical

Single Scan @ 10 ms: 400:1 Max per second with High Speed Averaging Mode: 3500:1	Signal to Noise S/N Ratio:
---	----------------------------

Hardware & Interface Connectivity

USB, RS-232	Computer Interface:
-------------	---------------------

Threading & Mounting

(3) 2-56	Mounting Threads:
----------	-------------------

Environmental & Durability Factors

0 to +55	Operating Temperature (°C):
-30 to +70	Storage Temperature (°C):

0.02 nm/°C	Thermal Stability:
------------	--------------------

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:

Compliant	Reach 250:
-----------	------------

United States	Country of Origin:
Edmund Optics India Private Limited	Imported By:

Product Details

- High Resolution Spectrometers for Narrow Peak Identification
- Spectral Ranges Spanning UV-VIS, VIS-NIR, and NIR Wavelengths
- Rapid Acquisition Speed and Excellent Thermal Stability

Ocean Optics HR High Resolution Spectrometers, available in HR2, HR4, and HR6 models, are designed to identify narrow spectral peaks with detailed spectral analysis for applications that require high-resolution solutions. The HR2 spectrometers feature high-resolution performance, fast scan speeds, and excellent thermal stability, providing rapid, real-time results ideal for applications such as plasma monitoring and pharmaceutical analysis. The HR4 spectrometers combine high-resolution spectral analysis with excellent thermal stability, making these models excel in precision-demanding environments such as DNA/RNA analysis, biomedical research, and high-throughput reflection testing. The HR6 spectrometers offer high sensitivity, high resolution, and excellent signal-to-noise ratio (SNR) performance for applications including protein absorbance and emission of broadband sources. The Ocean Optics HR High Resolution Spectrometers include the user-friendly OceanView software system to optimize spectrometer performance, ease system integration, and access data for analysis.