

[See all 10 Products in Family](#)

Coherent® Thermopile Power Sensor 1174262 | 5mW - 10W, USB

See More by [Coherent®](#)



Stock **#88-416** 2 In Stock

-

1

+

₹1,81,602

 Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1+	₹1,81,602 each
Need More?	Request Quote

Product Downloads

General	
PM10 Coherent Part Number: 1174262	Model Number:
Meterless	Type:

±2	Calibration Uncertainty (%):
----	------------------------------

0.5 - 10	Long Pulse Joule Mode Range (J):
Air	Cooling Method:
0.6 @ 1064nm, 10ns	Maximum Incident Energy Density (J/cm²):
Physical & Mechanical Properties	
19	Active Area Diameter (mm):
Optical Properties	
10600	Calibration Wavelength (nm):
190 - 11000	Wavelength Range (nm):
0.19 - 11	Wavelength Range (µm):
Sensor	
Thermopile	Type of Sensor:
Electrical	
30 (air-cooled)	Maximum Intermittent Power, <5min (W):
6	Maximum Incident Power Density (kW/cm²):
5mW - 10W	Power Range:
Hardware & Interface Connectivity	
2.5	Length of Cable (m):
USB	Computer Interface:
Regulatory Compliance	
Exempt	RoHS 2015:
Contains SVHC(s)	Reach 224:
View	Certificate of Conformance:
United States	Country of Origin:
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	Imported By:

Product Details

- Superior Damage Resistance
- Wide Dynamic Range
- ISO 17025 Certified

Coherent® Thermopile Power Sensors are ideal for measuring the average power of continuous wave lasers or pulsed laser energy. Thermopile sensors operate by absorbing and converting incident laser radiation into heat, which then flows to a heat sink. The temperature difference between the absorber and heat sink is converted into an electrical signal by a thermocouple junction. Coherent® Thermopile Power Sensors, unlike semiconductor sensors, do not saturate. Unlike semiconductor sensors, thermopile sensors feature high power capability and flat spectral response.