

[See all 5 Products in Family](#)

Coherent® High Sensitivity Optical Power Sensor 1098401 | UV, 250-400nm

See More by [Coherent®](#)



Stock #88-413 **3 In Stock**

1 MRP ₹1,00,890

! Price inclusive of all taxes

ADD TO CART

Volume Pricing

| | |
|------------|-------------------------------|
| Qty 1+ | ₹1,00,890 each |
| Need More? | Request Quote |

Product Downloads

General

OP-2 UV
Coherent Part Number: 1098401

Model Number:

[Meter required](#)

Type:

±8

Calibration Uncertainty (%):

Air **Cooling Method:**

Compatible Meters:
[#35-203](#), [#12-393](#), [#59-978](#),
[#88-411](#), [#66-277](#), [#88-412](#)

Physical & Mechanical Properties

6.0 **Active Area Diameter (mm):**

Optical Properties

250 - 400 **Wavelength Range (nm):**

Sensor

Silicon **Type of Sensor:**

Electrical

30 **Maximum Incident Beam Power (mW):**

10 **Minimum Incident Beam Power (nW):**

1 **Resolution (nW):**

10nW - 30mW **Power Range:**

Hardware & Interface Connectivity

1.8 **Length of Cable (m):**

DB-25 **Computer Interface:**

Regulatory Compliance

[Exempt](#) **RoHS 2015:**

[Contains SVHC\(s\)](#) **Reach 224:**

[View](#) **Certificate of Conformance:**

United States **Country of Origin:**

Imported By:
Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Product Details

- Utilize Silicon or Germanium Detectors
- Ideal for nW to Low mW CW Laser Measurements
- Removable Light Shield
- Compatible with [Coherent® Laser Power and Energy Meters](#)

Coherent® High Sensitivity Optical Power Sensors are semiconductor sensors designed for nanowatt to low milliwatt continuous wave laser measurements. These semiconductor sensors are available for detection from the ultraviolet to the infrared, and feature a removable light shield. An attenuator is also available that will boost power up to 5W.

Note: OP-2 sensors are compatible with the LabMax-Pro ([#35-203](#)), LabMax-TOP/TO ([#88-412](#)), FieldMaxI-TOP/TO ([#66-277](#)), and FieldMate ([#59-978](#)) meters.