


TECHSPEC[®] Polarization Maintaining Mirror, 532nm, 45° AOI, 12.7mm Dia., 6.35mm Thick



Polarization Phase Maintaining Mirrors

Stock **#26-868** **6 In Stock**

-

1

+

₹18,540

ADD TO CART

Volume Pricing	
Qty 1+	₹18,540 each
Need More?	Request Quote

Product Downloads

Physical & Mechanical Properties	
6.35	Thickness (mm):
12.70	Diameter (mm):
90	Clear Aperture (%):
Optical Properties	
Fused Silica	Substrate: ☐

45	Angle of Incidence (°):
Polarization Maintaining (532nm)	Coating:
532	Design Wavelength DWL (nm):
λ/8	Surface Flatness (P-V):
Coating Specification: R _{avg} S & P ≥ 99.90% @ 532 @ 45° AOI R _{avg} ≥ 99 % @ 510 – 550nm @ 45° AOI R _{avg} ≥ 80% @ 650nm @ 45° AOI	
Regulatory Compliance	
View	Certificate of Conformance:
United States	Country of Origin:
Edmund Optics India Private Limited	Imported By:

Product Details

- Preserves Incident Circular Polarization at 45° AOI
 - Up To 99.9% Reflection at 532 or 1064nm, and 80% at 650nm for Alignment
 - 12.7, 25.4, and 50.8mm Designs Available
- TECHSPEC Polarization Maintaining Mirrors preserve circular polarization direction upon reflection at a 45° angle of incidence. Featuring a standard laser V-Coat of 532 or 1064nm, these mirrors achieve a high reflection of ≥99.9%. Additionally, these mirrors offer a ≥80% reflectivity at 650nm to facilitate system alignment. TECHSPEC Polarization Maintaining Mirrors feature fused silica substrates and are available in standard diameters of 12.7, 25.4, and 50.8mm. These mirrors are ideal for applications which utilize and require the preservation of circular polarization, such as laser machining and interferometry.
- These polarization maintaining mirrors are especially well-suited for reflected beam paths in systems requiring critical polarization control. Their specialized dielectric coatings and surface quality help preserve the polarization state of incident light, supporting high-precision performance in applications such as interferometry, quantum optics, and polarization-sensitive laser systems. With high reflectivity across key wavelengths, they are ideal for free-space optical setups requiring consistent polarization alignment and beam fidelity.

Technical Information

