

[See all 40 Products in Family](#)

Power Supply for 10mW HeNe Laser, 24 VDC, Bare Wire Leads



DC with Bare Leads HeNe Laser Power Supply

Stock **#18-968** [CONTACT US](#)

1 [-](#) [+](#) MRP ₹42,480

Price inclusive of all taxes

ADD TO CART

Volume Pricing

Qty 1+	₹42,480 each
Need More?	Request Quote

Product Downloads



General

OEM **Type:**

[1135, 1135P](#) **Compatible Laser Models:**

L28 Series **Model Number:**

[#62-726, #62-727](#) **Compatible Laser Stock Number:**

Physical & Mechanical Properties

4.25 x 3.30 x 1.20	Dimensions (inches):
Electrical	
2.5-25	Output Power (W):
3.4 (Max. Current Draw)	Input Current (A):
Hardware & Interface Connectivity	
3100	Output Voltage (V):
6.5	Output Current (mA):
High Voltage Alden Connector	Connector:
20-30 DC	Input Voltage (V):
Regulatory Compliance	
View	Certificate of Conformance:
United States	Country of Origin:
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	Imported By:

Product Details

- Power Options from 0.5 - 22.5mW
- Improved Stability
- Ideal for Interferometry and Metrology Applications
- Random or Linear Polarization Options

Lumentum High Performance Helium-Neon Lasers feature a patented close-cathode design that provides improved thermal and power stability. They also utilize a patented field concentrator design that enables fast turn-on. These Lumentum HeNe lasers also feature precisely aligned cylindrical housings, with cylindrical laser heads and electrical interconnect systems used to simplify system integration. Lumentum High Performance Helium-Neon Lasers' rugged design is ideal for even the most demanding applications. They are exemplary for use within interferometry and metrology applications.

Note: Please exercise caution when using a user-provided power supply to not exceed the electrical specifications of the laser as this may cause damage and void the warranty. These HeNe lasers comply with 21CFR1040 and IEC 825-1:1993. Lumentum was previously known as JDSU.

Technical Information

Beam Expander Mounting Configurations

Click on an item below to be brought to that item's product page.

