

[See all 7 Products in Family](#)

Power Supply Kit for Prime Express & Retiga Scientific Cameras



Kit included with #90-390 Prime BSI Express camera & #90-394/#90-395 Retiga cameras

Stock #90-399 NEW **2 In Stock**

⊖ 1 ⊕ ₹21,750

ADD TO CART

Volume Pricing

Qty 1+	₹21,750 each
Need More?	Request Quote

Product Downloads

General

Camera Accessory **Type:**
Power supply with Cable **Contents of Kit:**

Regulatory Compliance

[View](#) **Certificate of Conformance:**

Canada **Country of Origin:**

Product Details

- Long Exposure CMOS (Over 60 Minutes)
- Feature Extended Dynamic Range (EDR)
- Dual Imaging Modes for Flexibility
- Scientific Cameras for High Sensitivity Microscopy Applications



Teledyne
Authorized
Distributor

Teledyne Photometrics Retiga E USB Cameras feature ultra-low dark current (<0.001 electrons/pixel/second), enabling exposure times of over an hour for low-light and long-duration imaging. The cameras feature EDR mode, which combines a large full-well capacity with low read noise to capture both intense and weak signals in the same image. The Retiga E series offers dual imaging modes; a long exposure mode enables ultra-sensitive, low-light imaging, and a fast capture mode for high-speed acquisition. The dual modes provide flexible performance for both static and dynamic scientific applications. Teledyne Photometrics Retiga E USB Cameras are ideal for time-lapse imaging in cell colony growth, fluorescence microscopy, and bioluminescence/chemiluminescence imaging. These cameras include Teledyne's proprietary-designed software platforms, Beacon and PVCAM, for optimizing camera performance and ease of system integration.
