

[See all 78 Products in Family](#)

Preloaded Norland Optical Adhesive NBA 108H Dispensing Barrel (10cc)

See More by [Norland](#)



10cc Dispensing Barrel for NOA (NOA60 shown as an example)

Stock #17-384 **2 In Stock**

1 MRP ₹4,195

● Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-4	₹4,195 each
Qty 5-11	₹3,781 each
Need More?	Request Quote

Product Downloads

General

0.34 Size (oz):

108H Norland Number:

4 months Shelf Life:

Barrel Type:

Typical Applications:

Temporary bonding of lenses to metal polishing mounts

Note:

Heat curing (-H suffix) adhesives are oxygen inhibited. If used on the surface of a substrate, the adhesive will need to be cured under an inert atmosphere (like nitrogen) to fully cure.

Optical Properties**Index of Refraction (n_d):**

1.51

Absorption Range (nm):

350 - 380

Material Properties**Glass Bonding:**

Excellent

Metal Bonding:

Excellent

Plastic Bonding:

Fair

Viscosity (cps):

550

Bonding Type:

Glass to Metal

Energy for Full Cure (J/cm^2):

6

Environmental & Durability Factors**Durability:**

Hard & Resilient

Regulatory Compliance**RoHS 2015:**

[Compliant](#)

Certificate of Conformance:

[View](#)

Reach 253:

[Compliant](#)

Country of Origin:

United States

Imported By:

Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Product Details

- Dispensing Syringes Preloaded with 2 or 10g of Adhesive
- Adhesives for Glass, Metal, and Plastic Bonding
- Require a Dispensing Unit & Dispenser Tips for Use
- [Applicator and Bulk Bottles](#) of Norland Adhesive Also Available

Preloaded Norland Optical Adhesive Syringes are pneumatic dispensing syringes preloaded with either 2g or 10g of Norland Optical Adhesive. Norland Optical Adhesives are one-part, UV curing adhesives that are used for glass, metal, and plastic bonding. A range of adhesives are available to meet specific application requirements such as ML-A-3920 for defense applications, low outgassing for aerospace applications, or UV transmission for UV optical applications. Preloaded Norland Optical Adhesive Syringes require a [dispensing unit](#) and [dispensing tips](#) for use and are ideal for applications requiring precise control of the amount of applied adhesive. Applicators and Bulk Bottles of Norland Adhesive are also available.

Technical Information

NORLAND OPTICAL ADHESIVES (NOA) APPLICATION NOTES

Title	Description
Applying Adhesive	Covers best practices to use when applying Norland Optical Adhesives to ensure an even adhesive layer while avoiding air bubbles.
Chemical Resistance of NOA	Covers the effects of various chemicals on Norland Optical Adhesives including acids, bases, and solvents.
Preventing Lens Separations with NOA	Covers best practices to avoid adhesive failures when bonding optical elements.
Separating Lenses Bonded with NOA	Covers how to unbond optical elements bonded with Norland Optical Adhesives.

;