

Polarization Maintaining Optical Fiber, PANDA, 1270-1625nm, 5m



Stock #72-900 **3 In Stock**

- 1 + ₹9,264

ADD TO CART

Volume Pricing

Qty 1+	₹9,264 each
Need More?	Request Quote

Product Downloads

General

PM **Type:**

Physical & Mechanical Properties

125.0 ± 1.0 **Cladding Diameter (µm):**

5 **Length (m):**

8 **Core Diameter (µm):**

Coating Diameter:

245.0 ± 15.0

Optical Properties

0.12 **Numerical Aperture NA:**

≤ 1.0 dB/km @ 1300 nm **Attenuation (dB/km):**

1270 - 1625 **Wavelength Range (nm):**

9.3 ± 0.5 @ 1300 nm **Mode Field Diameter (nm):**

Regulatory Compliance

[View](#) **Certificate of Conformance:**

United States **Country of Origin:**

Edmund Optics India Private Limited **Imported By:**

Product Details

- Single Mode and Polarization Maintaining Options
- 5, 10, and 20m Lengths
- Transmission Options from 450nm to 1625nm

Bare Fiber Strands are cladded step index fibers with no sheath manufactured by Coherent and Corning to allow for easy integration in space constrained systems. These fiber spools allow for direct access to the core, facilitating precise measurements and connections as well as allowing for modification to the lengths as needed. Featuring various wavelength ranges spanning the VIS and IR spectra, these fiber spools cover a wide range of applications that require specific wavelengths and provide tight cutoff tolerances. Bare Fiber Strands are designed with core diameters of 3.0µm up to 8.2µm and numerical apertures ranging from 0.12 to 0.14.

;