

Polarization Maintaining Optical Fiber, PANDA, 620-850nm, 5m



Stock #72-906 **3 In Stock**

MRP ₹12,425

Price inclusive of all taxes

ADD TO CART

Volume Pricing

Qty 1-4	₹12,425 each
Qty 5-24	₹11,183 each
Need More?	Request Quote

Product Downloads

General

PM Type:

Physical & Mechanical Properties

125.0 ± 1.0 Cladding Diameter (µm):

5 Length (m):

Core Diameter (µm):

3.5

Coating Diameter:

245.0 ± 15.0

Optical Properties

Numerical Aperture NA:

0.12

Attenuation (dB/km):

≤ 15.0 dB/km @ 630 nm

Wavelength Range (nm):

620 - 850

Mode Field Diameter (nm):

4.5 ± 0.5 @ 630 nm

Regulatory Compliance

Certificate of Conformance:

[View](#)

Country of Origin:

United States

Imported By:

Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Product Details

- Single Mode and Polarization Maintaining Options
- 5, 10, and 20m Lengths
- Transmission Options from 450nm to 1625nm

Bare Fiber Strands are cladded step index fibers with no sheath manufactured by Coherent and Corning to allow for easy integration in space constrained systems. These fiber spools allow for direct access to the core, facilitating precise measurements and connections as well as allowing for modification to the lengths as needed. Featuring various wavelength ranges spanning the VIS and IR spectra, these fiber spools cover a wide range of applications that require specific wavelengths and provide tight cutoff tolerances. Bare Fiber Strands are designed with core diameters of 3.0µm up to 8.2µm and numerical apertures ranging from 0.12 to 0.14.