

[See all 35 Products in Family](#)

Polarization Maintaining Patchcord, FC/APC, 0.12NA, 460-700nm, 1m



FC/APC Connector

Stock #25-979 **3 In Stock**

MRP ₹26,231

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-4	₹26,231 each
Qty 5-24	₹23,576 each
Need More?	Request Quote

Product Downloads

General

Patchcord **Type:**

PM460-HP **Fiber Cable Type:**

Aligned to Connector Key **Slow Axis Alignment:**

Physical & Mechanical Properties

Length (m):
1 +0.075/-0.0

Jacket Material:
Ø3 mm Blue PVC Furcation Tubing

Key Width:
2mm Narrow Key Connector Key Aligned with Slow Axis

Optical Properties

Numerical Aperture NA:
0.12

Alignment Wavelength (nm):
488

Wavelength Range (nm):
460 - 700

Mode Field Diameter (nm):
3.3 ± 0.5µm @ 515nm

Extinction Ratio:
18dB (Min)
20dB (Typ.)

Hardware & Interface Connectivity

Connector:
FC/APC

Insertion Loss (dB):
1.50dB (Max)
1.20dB (Typ.)

Loss (dB):
60

Environmental & Durability Factors

Operating Temperature (°C):
0 to 70

Storage Temperature (°C):
-45 to 85

Regulatory Compliance

RoHS 2015:
[Compliant](#)

Certificate of Conformance:
[View](#)

REACH 241:
[Compliant](#)

Country of Origin:
United States

Imported By:
Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- FC/PC, FC/APC, and Hybrid Terminated Connectors
- Patchcords for Wavelengths from 460 – 1625nm
- Polarization Extinction Ratios up to 25dB
- 1m and 2m Standardized Lengths Available

Polarization Maintaining Fiber Optic Patchcords are available with FC/PC or FC/APC terminated connectors. Hybrid terminated connectors enable users to adapt FC/PC or FC/APC patchcords for compatibility with existing fiber assemblies. Typical extinction ratios between 18 – 25dB maintain input polarization orientation. Polarization Maintaining Fiber Optic Patchcords are ideal for applications including beam delivery, telecommunications, fiber optic sensing. Each connector is engraved with the fiber type for easy integration and identification.

