

[See all 14 Products in Family](#)

Schott KL 2500 LED Light Source

See More by [SCHOTT Optical Components](#)



Stock #72-135 **2 In Stock**

- 1 + ₹1,54,521

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1+	₹1,54,521 each
Need More?	Request Quote

Product Downloads

General

>50,000 **Operating Lifetime (hours):**

250.400 **Model Number:**

Yes **Intensity Control Option:**

LED Illuminator **Type of Illumination:**

Manufacturer:

SCHOTT

Illumination Mode:

Constant

Physical & Mechanical Properties

Dimensions (mm):

114L x 231W x 137H

Weight (kg):

3.6

Optical Properties

Color:

White

Electrical

Output Power (Lumens):

1,100

Hardware & Interface Connectivity

Input Voltage (V):

24 DC

Power Supply:

Power Cord Required and Sold Separately.

USA: [#16-792](#)

Europe: [#18-492](#)

Japan: [#78-580](#)

Korea: [#16-792](#)

China: [#16-792](#)

UK: [#18-493](#)

Switzerland: [#18-494](#)

Environmental & Durability Factors

Color Temperature (K):

5600

Regulatory Compliance

Certificate of Conformance:

[View](#)

Country of Origin:

Czech Republic

Imported By:

Edmund Optics India Private Limited

Product Details

- Maximum Light Intensity of 1100 Lumens
- Continuous Dimming from 0 - 100%
- Various Light Guide Options Available
- Ideal for Use with Stereo Microscopes

SCHOTT KL Fiber Optic Light Sources are LED cold light sources that produce intense, but heat free light for microscopy applications. Combining the efficient light output of the light engine with various light guide geometries offers significantly higher intensities compared to direct LED light. Two light source models are available, the KL 1600 which features a 680 lumens maximum intensity and the KL 2500 which features an 1100 lumens maximum intensity with an extra-fine dimming option. SCHOTT KL Fiber Optic Light Sources are ergonomically designed to have a small footprint, allowing them to be easily integrated into compact benchtop lab settings. The uniform light quality of the KL Series is ideal for biological, geological, and pathological stereo microscope applications.

Note: Power cord sold separately.

Technical Information



