

Schott MC-LS Cool White Light Source

See More by [SCHOTT Optical Components](#)



Stock #75-282 NEW **1 In Stock**

MRP ₹86,553

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1+	₹86,553 each
Need More?	Request Quote

Product Downloads

General

Operating Lifetime (hours):
>50,000

Model Number:
A20990

Intensity Control Option:
Yes

Type of Illumination:
LED Illuminator

Manufacturer:

SCHOTT

Illumination Mode:

Constant

Physical & Mechanical Properties

Dimensions (mm):

158L x 145W x 98H

Weight (kg):

2

Optical Properties

Color:

White

Electrical

Output Power (Lumens):

850

Hardware & Interface Connectivity

Input Voltage (V):

100-240 AC

Power Supply:

Power Cord Required and Sold Separately.

USA: [#75-296](#)

Europe: [#75-298](#)

UK: [#75-297](#)

China: [#75-296](#)

Japan: [#78-580](#)

Korea: Not Available

Environmental & Durability Factors

Operating Temperature (°C):

0 to 40

Color Temperature (K):

5400

Regulatory Compliance

Certificate of Conformance:

[View](#)

Country of Origin:

Germany

Imported By:

Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Product Details

- Heat-Free, Remote Fiber-Optic Illumination
- Designed for Stereo Microscopy and Machine Vision Applications
- Two Light Source Models Available

SCHOTT ColdVision Fiber Optic Illuminators are engineered to deliver uniform light quality while minimizing the thermal impact on illuminated objects. Light sources, light guides, and various mechanical and optical accessories allow for easily customizable illumination based on machine vision or microscopy applications. SCHOTT ColdVision Fiber Optic Illuminators are available in two light source models, the CV-LS series and the MC-LS model. Available in Cool White or RGBW, the CV-LS series contains an optical feedback loop that controls light intensity for consistent, reproducible results in industrial inspection applications. The MC-LS model offers a maximum light intensity of 850 lumens and supports continuous dimming from 0 to 100%, accommodating all levels of stereo microscopy.

Note: Power cord sold separately. See specifications for specific products.