

[See all 40 Products in Family](#)

## Power Supply for 1.5-2.0mW HeNe Laser, 24 VDC, Bare Wire Leads



L28 Series with CDRH Delay HeNe Laser Power Supply

Stock **#11-385** [CONTACT US](#)

-

1

+

 ₹36,108

Price inclusive of all taxes

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1+         | ₹36,108 each                  |
| Need More?     | <a href="#">Request Quote</a> |

### Product Downloads



### General

Type:

OEM

Compatible Laser Models:

[1101](#), [1101P](#), [1103](#), [1103P](#), [1122](#), [1122P](#)

Model Number:

L28 Series

Compatible Laser Stock Number:

[#62-718](#), [#62-719](#), [#62-720](#), [#62-721](#), [#64-103](#), [#64-104](#)

|                                     |  |                             |
|-------------------------------------|--|-----------------------------|
| CDRH Delay (3-5 seconds)            |  | Features:                   |
| Physical & Mechanical Properties    |  |                             |
| 4.00 x 1.50 x 1.00                  |  | Dimensions (inches):        |
| Electrical                          |  |                             |
| 8.33                                |  | Output Power (W):           |
| 1.36 (Max. Current Draw)            |  | Input Current (A):          |
| Hardware & Interface Connectivity   |  |                             |
| 1700                                |  | Output Voltage (V):         |
| 4.9                                 |  | Output Current (mA):        |
| High Voltage Alden Connector        |  | Connector:                  |
| 24 DC                               |  | Input Voltage (V):          |
| Regulatory Compliance               |  |                             |
| <a href="#">View</a>                |  | Certificate of Conformance: |
| United States                       |  | Country of Origin:          |
| Edmund Optics India Private Limited |  | Imported By:                |

## Product Details

- Power Options from 0.5 - 22.5mW
- Improved Stability
- Ideal for Interferometry and Metrology Applications
- Random or Linear Polarization Options

Lumentum High Performance Helium-Neon Lasers feature a patented close-cathode design that provides improved thermal and power stability. They also utilize a patented field concentrator design that enables fast turn-on. These Lumentum HeNe lasers also feature precisely aligned cylindrical housings, with cylindrical laser heads and electrical interconnect systems used to simplify system integration. Lumentum High Performance Helium-Neon Lasers' rugged design is ideal for even the most demanding applications. They are exemplary for use within interferometry and metrology applications.

**Note:** Please exercise caution when using a user-provided power supply to not exceed the electrical specifications of the laser as this may cause damage and void the warranty. These HeNe lasers comply with 21CFR1040 and IEC 825-1:1993. Lumentum was previously known as JDSU.

## Technical Information

### Beam Expander Mounting Configurations

Click on an item below to be brought to that item's product page.

