

[See all 186 Products in Family](#)

Hoya R72 (720nm), 12.5mm Dia., 2.5mm Thick, Colored Glass Longpass Filter

See More by [Hoya](#)



Stock **#66-046** 20+ In Stock

-

1

+

₹2,569

ADD TO CART

Volume Pricing	
Qty 1-10	₹2,569 each
Qty 11-49	₹2,258 each
Need More?	Request Quote

Product Downloads

General

Type:

Longpass Filter

Physical & Mechanical Properties

Diameter (mm):

12.50

Thickness (mm):

2.50 ±0.2

Dimensional Tolerance (mm):

±0.38	
Protective as needed	Bevel:
Optical Properties	
720±9	Cut-Off Position λ_c (nm):
720.00 ±9	Cut-On Wavelength (nm):
Hoya R72	Glass/Filter Number:
Colored Glass	Substrate: □
Uncoated	Coating:
Black	Color:
80-50	Surface Quality:
IR	Wavelength:
0.92	Reflection Factor P _d :
<45	$\Delta\lambda$ (nm):
>85	TH (%):
Material Properties	
2.86	Density (g/cm ³):
525	Transformation Temperature (°C):
Regulatory Compliance	
Exempt	RoHS 2015:
Compliant	Reach 224:
View	Certificate of Conformance:
United States	Country of Origin:
Edmund Optics India Private Limited	Imported By:

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- UV, VIS and IR Pass Ranges
- VIS Can Be Used for Color Bandpass
- Also Available [Mounted](#)

Hoya Colored Glass Longpass Filters feature a colored glass substrate. These filters are manufactured from substrates with inherently different absorption and transmission properties across a specific spectral region. Hoya Colored Glass Longpass Filters have UV, VIS, and IR pass ranges. A longpass filter has low transmission in the shortwave region (stopband) and high transmission in the longwave region (passband). These filters are also available in a [mounted](#) version.

Longpass Filter Kits

Longpass filter kits are available in three different options: UV-VIS, VIS, or VIS-NIR. Each kit contains 8 filters in either 12.5mm diameter, 1" diameter, or 2" square.

UV-VIS Kit Contains: WG 295, WG 305, WG 320, L 37, GG 400, GG 420, GG 435, GG 455

VIS Kit Contains: GG 475, GG 495, OG 515, OG 530, OG 550, OG 570, OG 590, RG 610

VIS-NIR Kit Contains: RG 630, RG 665, RG 695, RG 715, RG 780, RG 830, RG 850, RG 1000

Complete Filter Kits


Complete filter kits are available with 12.5mm diameter, 50.0mm diameter, 1" diameter, or 2" square filters. Each kit contains all 37 Longpass Glass Color Filter types.

Note: Due to supply chain issues, our kits may be delivered with an alternative packaging solution in place of a wooden box. For any questions, please contact kits@edmundoptics.com.

Filter Simulation Software

[Click here](#) to download HOYA's colored glass filter simulation software which can be used to calculate the internal transmittance and external transmission of each HOYA glass type. The software can simulate the performance of individual filters with user specified thickness.

Technical Information



λ_s	limit of stopband: specified at 0.001% internal transmittance
λ_c	cut-off position: specified at 50% internal transmittance
λ_p	limit of the passband
τ_p	internal spectral transmittance at λ_p
ρ	density
T_g	transformation temperature

Compatible Mounts