


[See all 13 Products in Family](#)

Set of 3, 1" Stackable, Magnetic ND Filters for WinCamD-LCM with Caps and Alignment Targets



Stock **#71-561** 1 In Stock

-

1

+

₹99,000

ADD TO CART

Volume Pricing	
Qty 1+	₹99,000 each
Need More?	Request Quote

Product Downloads

General	
Filters are mounted at 2° to axis.	Note:
Includes MagND-1, MagND-2, MagND-3	
Contents of Kit:	
Regulatory Compliance	
View	Certificate of Conformance:
United States	Country of Origin:
Edmund Optics India Private Limited	Imported By:

Product Details

- ISO11146 Compliant
- 355 - 1150nm or 2000 - 16000nm Wavelength Options
- 50mm and 200mm Travel Options

DataRay M² Measurement Systems combine a beam profiling camera mounted on an automated translation stage to make an all-in-one M² measurement system. M², or Beam Quality Factor, characterizes the degree of imperfection in a real-world laser beam relative to a perfect TEM00 beam, and is a common acceptance criterion for laser or laser system manufacturing. These systems operate by moving the mounted beam profiler through the beam waist to perform ISO 11146 compliant measurements and are available with 50 or 200mm travel lengths, and two wavelength range options of 355 - 1150nm or 2000 - 16000nm. DataRay M² Measurement Systems are designed with an easy-to-setup USB3 system, intuitive software interface, and have a variety of accessories available separately. These measurements systems are ideal for measuring a wide range of M² on pulsed and CW lasers.