

## Single Mode Optical Fiber 600-770nm, 20m



Stock #72-895 [CONTACT US](#)

- 1 + MRP ₹10,013

**i** Price inclusive of all taxes

**ADD TO CART**

### Volume Pricing

Qty 1+	₹10,013 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

### General

SM **Type:**

### Physical & Mechanical Properties

125.0 ± 1.0 **Cladding Diameter (µm):**

20 **Length (m):**

3.5 **Core Diameter (µm):**

245.0 ± 15.0 **Coating Diameter:**

## Optical Properties

0.13 **Numerical Aperture NA:**

≤ 12.0 dB/km @ 630 nm **Attenuation (dB/km):**

600 - 770 **Wavelength Range (nm):**

4.0 ± 0.5 @ 630 nm **Mode Field Diameter (nm):**

## Regulatory Compliance

[View](#) **Certificate of Conformance:**

United States **Country of Origin:**

**Imported By:**  
Edmund Optics India Private Limited  
267, Greystone Building, Second Floor,  
6th Cross Rd, Binnamangala,  
Stage 1, Indiranagar, Bengaluru,  
Karnataka, India 560038  
Phone: +91- 80-6845 0000

## Product Details

- Single Mode and Polarization Maintaining Options
- 5, 10, and 20m Lengths
- Transmission Options from 450nm to 1625nm

Bare Fiber Strands are cladded step index fibers with no sheath manufactured by Coherent and Corning to allow for easy integration in space constrained systems. These fiber spools allow for direct access to the core, facilitating precise measurements and connections as well as allowing for modification to the lengths as needed. Featuring various wavelength ranges spanning the VIS and IR spectra, these fiber spools cover a wide range of applications that require specific wavelengths and provide tight cutoff tolerances. Bare Fiber Strands are designed with tight diameters of 3.0µm up to 8.2µm and numerical apertures ranging from 0.12 to 0.14.