

Single Mode Optical Fiber 780-970nm, 10m



Stock #72-892 **2 In Stock**

1 MRP ₹6,266

● Price inclusive of all taxes

ADD TO CART

Volume Pricing

Qty 1-4	₹6,266 each
Qty 5-24	₹5,639 each
Need More?	Request Quote

Product Downloads

General

SM Type:

Physical & Mechanical Properties

125.0 ± 1.0 Cladding Diameter (µm):

10 Length (m):

Core Diameter (µm):

4.4

245.0 ± 15.0

Coating Diameter:

Optical Properties

0.13 **Numerical Aperture NA:**

≤ 3.5 dB/km @ 850 nm ≤ 4.0 dB/km @ 780 nm **Attenuation (dB/km):**

780 - 970 **Wavelength Range (nm):**

5.0 ± 0.5 @ 850 nm **Mode Field Diameter (nm):**

Regulatory Compliance

[View](#) **Certificate of Conformance:**

United States **Country of Origin:**

Imported By:
Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Product Details

- Single Mode and Polarization Maintaining Options
- 5, 10, and 20m Lengths
- Transmission Options from 450nm to 1625nm

Bare Fiber Strands are cladded step index fibers with no sheath manufactured by Coherent and Corning to allow for easy integration in space constrained systems. These fiber spools allow for direct access to the core, facilitating precise measurements and connections as well as allowing for modification to the lengths as needed. Featuring various wavelength ranges spanning the VIS and IR spectra, these fiber spools cover a wide range of applications that require specific wavelengths and provide tight cutoff tolerances. Bare Fiber Strands are designed with core diameters of 3.0µm up to 8.2µm and numerical apertures ranging from 0.12 to 0.14.