

[See all 58 Products in Family](#)

# SCHOTT BG66, 100 x 80mm, 4.5mm Thick, Matte Plate Bandpass Filter

See More by [SCHOTT Optical Components](#)



Stock #26-911 **4 In Stock**

MRP ₹39,449

**!** Price inclusive of all taxes

**ADD TO CART**

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-10       | ₹39,449 each                  |
| Qty 11+        | ₹34,808 each                  |
| Need More?     | <a href="#">Request Quote</a> |

## Product Downloads

### General

Bandpass Filter **Type:**

### Physical & Mechanical Properties

100.0 x 80.0 **Dimensions (mm):**

100.00 **Length (mm):**

4.50 ±0.5 Thickness (mm):

80.00 Width (mm):

Break Edges Edges:

## Optical Properties

514.00 Center Wavelength CWL (nm):

SCHOTT BG66 Glass/Filter Number:

Uncoated Coating:

Blue-Green Color:

1.54 Index of Refraction (n<sub>d</sub>):

NIR Cutoff Wavelength:

## Material Properties

2.85 Density (g/cm<sup>3</sup>):

416 Transformation Temperature (°C):

## Regulatory Compliance

View Certificate of Conformance:

Germany Country of Origin:

Imported By:  
Edmund Optics India Private Limited  
267, Greystone Building, Second Floor,  
6th Cross Rd, Binnamangala,  
Stage 1, Indiranagar, Bengaluru,  
Karnataka, India 560038  
Phone: +91-80-6845 0000

## Product Details

- Unpolished Colored Glass Plates
- Large Raw Material Sizes up to 165 x 165mm
- Available in All [SCHOTT Colored Glass Types](#)
- [Polished SCHOTT Colored Glass Filters](#) Also Available

SCHOTT Matte Colored Glass Filter Plates are unpolished plates of colored glass that are used as raw material to manufacture [SCHOTT Colored Glass Filters](#). With large standard sizes up to 165 x 165mm, these plates can be cut, ground, and polished to meet application requirements for a wide range of filter sizes. SCHOTT Matte Colored Glass Filter Plates are available in all [SCHOTT colored glass types](#), including shortpass (heat absorbing), longpass, bandpass, and neutral density. To learn more about how our custom optical colored glass filter capabilities can be used for your application, see our [capabilities page](#).

Quote Your Size

;