

[See all 40 Products in Family](#)

Single Mode Patchcord, FC/PC, 0.14NA, 1260-1625nm, 5m



Stock #71-136 **1 In Stock**

- 1 + MRP ₹5,310

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-4	₹5,310 each
Qty 5-24	₹4,779 each
Need More?	Request Quote

Product Downloads

General

Patchcord **Type:**

SMF-28 Ultra **Fiber Cable Type:**

Physical & Mechanical Properties

Cladding Diameter (µm):

125 ± 0.7

5

Length (m):

Jacket Material:

900µm Yellow Hytel® Tubing

Coating Diameter:

242 ± 5µm

Optical Properties

Numerical Aperture NA:

0.13

Attenuation (dB/km):

≤0.32dB/km @ 1310nm ≤0.18dB/km @ 1550nm

Wavelength Range (nm):

1260 - 1625

Mode Field Diameter (nm):

9.2 ± 0.4µm @ 1310nm

10.4 ± 0.5µm @ 1550nm

Hardware & Interface Connectivity

Connector:

FC/PC

Insertion Loss (dB):

0.3 @ 1310nm

Regulatory Compliance

Certificate of Conformance:

[View](#)

REACH 241:

[Compliant](#)

Country of Origin:

United States

Imported By:

Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- FC/PC, FC/APC, and Hybrid Terminated Connectors
- Patchcords for Wavelengths from 450 – 1650nm
- 1m, 2m and 5m Standardized Lengths Available

Single Mode Fiber Optic Patchcords are available with FC/PC or FC/APC terminated connectors. Hybrid terminated connectors enable users to adapt FC/PC or FC/APC patchcords for compatibility with existing fiber assemblies. Designed for use with lasers from 450 – 1650nm in 1m, 2m and 5m standard lengths, these Single Mode Fiber Optic Patchcords are ideal for applications including beam delivery, microscopy, and telecommunications. Each connector is engraved with the fiber type for easy integration and identification.