

Schott CV 51mm Line Light

See More by [SCHOTT Optical Components](#)



Stock #75-290 NEW **1 In Stock**

⊖ 1 ⊕ ₹44,933

ADD TO CART

Volume Pricing	
Qty 1+	₹44,933 each
Need More?	Request Quote

Product Downloads

General

A08589	Model Number:
Line Light	Type:
Cylindrical Lens for 51mm Line Light	Compatible Product:
51 x 0.89	Line Dimensions:

Physical & Mechanical Properties

978.00 **Length (mm):**

Regulatory Compliance

[View](#) **Certificate of Conformance:**

Country of Origin:
Germany

Imported By:
Edmund Optics India Private Limited

Product Details

- Heat-Free, Remote Fiber-Optic Illumination
- Designed for Stereo Microscopy and Machine Vision Applications
- Two Light Source Models Available

SCHOTT ColdVision Fiber Optic Illuminators are engineered to deliver uniform light quality while minimizing the thermal impact on illuminated objects. Light sources, light guides, and various mechanical and optical accessories allow for easily customizable illumination based on machine vision or microscopy applications. SCHOTT ColdVision Fiber Optic Illuminators are available in two light source models, the CV-LS series and the MC-LS model. Available in Cool White or RGBW, the CV-LS series contains an optical feedback loop that controls light intensity for consistent, reproducible results in industrial inspection applications. The MC-LS model offers a maximum light intensity of 850 lumens and supports continuous dimming from 0 to 100%, accommodating all levels of stereo microscopy.

Note: Power cord sold separately. See specifications for specific products.
