

# Schott CV-LS Cool White Light Source

See More by [SCHOTT Optical Components](#)



Stock #75-279 **NEW** [CONTACT US](#)

- 1 + MRP ₹1,78,416

Price inclusive of all taxes

**ADD TO CART**

### Volume Pricing

Qty 1+	₹1,78,416 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

### General

>50,000 **Operating Lifetime (hours):**

A20980/6000K **Model Number:**

Yes **Intensity Control Option:**

LED Illuminator **Type of Illumination:**

**Manufacturer:**

SCHOTT

**Illumination Mode:**

Constant

## Physical & Mechanical Properties

**Dimensions (mm):**

129W x 201D x 59.69H

**Weight (kg):**

0.816

## Optical Properties

**Color:**

Cool White

## Electrical

**Output Power (Lumens):**

1350

## Hardware & Interface Connectivity

**Input Voltage (V):**

24 DC

**Power Supply:**

Power Cord Required and Sold Separately.

USA: [#75-296](#)

Europe: [#75-298](#)

UK: [#75-297](#)

China: [#75-296](#)

Japan: [#78-580](#)

Korea: Not Available

## Environmental & Durability Factors

**Operating Temperature (°C):**

0 to 45

**Color Temperature (K):**

6000

## Regulatory Compliance

**Certificate of Conformance:**

[View](#)

**Country of Origin:**

Germany

**Imported By:**

Edmund Optics India Private Limited  
267, Greystone Building, Second Floor,  
6th Cross Rd, Binnamangala,  
Stage 1, Indiranagar, Bengaluru,  
Karnataka, India 560038  
Phone: +91- 80-6845 0000

## Product Details

- Heat-Free, Remote Fiber-Optic Illumination
- Designed for Stereo Microscopy and Machine Vision Applications
- Two Light Source Models Available

SCHOTT ColdVision Fiber Optic Illuminators are engineered to deliver uniform light quality while minimizing the thermal impact on illuminated objects. Light sources, light guides, and various mechanical and optical accessories allow for easily customizable illumination based on machine vision or microscopy applications. SCHOTT ColdVision Fiber Optic Illuminators are available in two light source models, the CV-LS series and the MC-LS model. Available in Cool White or RGBW, the CV-LS series contains an optical feedback loop that controls light intensity for consistent, reproducible results in industrial inspection applications. The MC-LS model offers a maximum light intensity of 850 lumens and supports continuous dimming from 0 to 100%, accommodating all levels of stereo microscopy.

**Note:** Power cord sold separately. See specifications for specific products.