

SCHOTT N-WG320, 50mm Sq., 2mm Thick, Colored Glass Longpass Filter

See More by [SCHOTT Optical Components](#)



Stock **#14-470** 10 TO 12 DAYS

- 1 +

₹6,743.00

ADD TO CART

Qty 1-10
₹6,743.00
Qty 11+
₹6,612.00
Volume Pricing
Request Quote

Get Product Downloads
Dimensions (mm): 50.0 x 50.0
Cut-On Wavelength (nm): 320.00 ±6
Density (g/cm³):

2.51
Glass/Filter Number: SCHOTT N-WG320
Length (mm): 50.00
Coating: Uncoated
Color: Clear
Passband Limit 1 λ_{p1} (nm): 470
Index of Refraction n_d: 1.52
Spectral Transmittance t_p (%): 92
Stopband Limit λ_s(nm): 280
Surface Quality: 60-40
Transformation Temperature (°C): 563
Thickness (mm): 2.00 $\pm$ 0.2
Type: Longpass Filter
Wavelength: UV
Width (mm): 50.00
Dimensional Tolerance (mm): $\pm$ 0.2
Reflection Factor P_d: 0.92
Bevel: Protective as needed

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View