

## SugarCUBE™ Light Guide Adapter - 3mm



SugarCUBE™ Light Guide Adapter - 3mm (#13-536)

Stock **#13-536** **1 In Stock**

1  MRP ₹3,717

Price inclusive of all taxes

**ADD TO CART**

### Volume Pricing

Qty 1+	₹3,717 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

### Regulatory Compliance

**Compliant** RoHS 2015:

**Compliant** Reach 224:

**View** Certificate of Conformance:

United States Country of Origin:

**Imported By:**


Edmund Optics India Private Limited  
 267, Greystone Building, Second Floor,  
 6th Cross Rd, Binnamangala,  
 Stage 1, Indiranagar, Bengaluru,  
 Karnataka, India 560038  
 Phone: +91- 80-6845 0000

**Product Details**

- NA= 0.55
- No Packing Fraction Loss
- Excellent UV Transmission Properties
- Higher Overall Transmission than Glass Bundles

Liquid Light Guides are ideal for visible and ultraviolet illumination requirements. Unlike glass light guides, liquid guides do not suffer from packing fraction losses—spaces between fibers that cause reduced coupling efficiency (see diagram). These liquid guides cut off the near infrared spectrum, yielding both optimum transmission for visible applications and smaller bandpass for higher contrast color images. Liquid Light Guides have reduced long-wavelength transmission, which results in slightly bluer, higher color temperature output. Repeated handling of liquid light guides does not result in the breakage typical of glass bundles, which reduces efficiency over time. The light guides use quartz windows to seal in non-toxic transmissive medium. These liquid light guides connect to illuminators and filter mounts via the Fiber Optic Adapter [#38-944](#).

**Technical Information**



Core Diameter	A	B	C	D	E	Stock No.
3mm	0.312"	0.43"	0.50"	0.31"	0.27"	<a href="#">#53-689</a>
3mm	0.312"	0.43"	0.50"	0.31"	0.27"	<a href="#">#53-692</a>
4mm	0.312"	0.50"	0.50"	0.39"	0.37"	<a href="#">#53-690</a>
4mm	0.312"	0.50"	0.50"	0.39"	0.37"	<a href="#">#53-693</a>
5mm	0.312"	0.56"	0.60"	0.43"	0.41"	<a href="#">#53-691</a>
5mm	0.312"	0.56"	0.60"	0.43"	0.41"	<a href="#">#53-694</a>

