

# USPOT UV Spot Light



Stock #26-820 [CONTACT US](#)

1 [-](#) [+](#) MRP ₹5,20,001

Price inclusive of all taxes

**ADD TO CART**

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1+         | ₹5,20,001 each                |
| Need More?     | <a href="#">Request Quote</a> |

## Product Downloads

### Physical & Mechanical Properties

**Dimensions (mm):**  
Spot Light: 45mm Dia x 155.5mm Length  
Driver: 300 x 210 x 101

### Optical Properties

**Wavelength (nm):**  
365.00

**Beam Diameter (mm):**

20 @ 10mm WD, 30 @ 40mm WD

**Working Distance (mm):**  
5 - 200

**Irradiance (W/cm<sup>2</sup>):**  
3.30

## Hardware & Interface Connectivity

**Power Requirement:**  
AC 100 - 240V

## Regulatory Compliance

**Certificate of Conformance:**  
[View](#)

**Country of Origin:**  
France

**Imported By:**  
Edmund Optics India Private Limited  
267, Greystone Building, Second Floor,  
6th Cross Rd, Binnamangala,  
Stage 1, Indiranagar, Bengaluru,  
Karnataka, India 560038  
Phone: +91- 80-6845 0000

## Product Details

- Up to 3.30W/cm<sup>2</sup> UV Irradiance
- 365nm Center Wavelength
- Ideal for Automated Production Lines

Mounted UV Curing LED Light Sources provide 365nm adjustable UV irradiance up to 3.30W/cm<sup>2</sup> and feature an integrated optical system to ensure high output power at large working distances. The mounted UV spot light comes with a standalone power supply and controller for easy benchtop operation as well as control over the light intensity and exposure time. In addition, this mounted UV spot light can be controlled directly with a programmable logic controller (PLC) which provides temperature monitoring, UV irradiance control, and insulation time control. Mounted UV Curing LED Light Sources are ideal for automated production lines across a wide range of applications and industries such as UV curing for coatings and resins on electronics, UV assembly and encapsulation of opto-electronics, and UV curing of glues in cosmetics manufacturing. M3 mounting holes on the compact 172 x 71 x 71mm housing make for easy integration into production lines and OEM operations.