

[See all 17 Products in Family](#)

SI Free-Space Balanced Photoreceiver, 320-1000nm



#90-639 SI Free-Space Balanced Photoreceiver, 320-1000nm

Stock #90-639 **NEW** 2 In Stock

1 MRP ₹3,71,700

Price inclusive of all taxes

ADD TO CART

Volume Pricing

Qty 1+	₹3,71,700 each
Need More?	Request Quote

Product Downloads

General

Note:

- Includes:
- (2) Threaded coupler ring
 - Lemo®3-pin connector
 - (3) Adapter SMA (male) to BNC (female)
 - Datasheet

Physical & Mechanical Properties

Weight (g): 410

Dimensions (mm):

Optical Properties

320 - 1000 nm **Spectral Range:**

Sensor

Si-PIN photodiode **Detector Type:**

Electrical

2×10^4 or 6×10^4 (switchable) **Transimpedance Gain (Ω):**

7.4×10^{-12} @880nm **Noise Equivalent Power NEP (W/ Hz^{1/2}):**

100 MHz **Bandwidth (-3 db):**

± 1.0 V at 50 Ω load (for linear gain and low harmonic distortion), maximum ± 2.0 V at 50 Ω load **Output Signal:**

10.8×10^3 or 32.4×10^3 @850 nm switchable **Conversion Gain (V/W):**

50 **Common Mode Rejection (dB):**

Hardware & Interface Connectivity

± 15 V (± 14.5 V ... ± 16.5 V) -90 / +120 mA **Power Requirement:**

Power Supply Required and Sold Separately.
USA: [#59-180](#)
Europe: [#59-180](#)
Japan: Not Available
Korea: Not Available
China: [#59-180](#) **Power Supply:**

Environmental & Durability Factors

0 to +60 **Operating Temperature ($^{\circ}$ C):**

Regulatory Compliance

[Compliant](#) **RoHS 2015:**

[View](#) **Certificate of Conformance:**

Germany **Country of Origin:**

Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000 **Imported By:**

Product Details

- Subtracts Two Photodiode Signals for Differential Detection
- Improved Signal to Noise Ratio (SNR) for Weak or Modulated Optical Signals
- High Common-Mode Noise Suppression for Improved Measurement Sensitivity and Accuracy
- Available in Si and InGaAs models for UV-VIS and NIR spectral ranges

Balanced Photoreceivers use true differential detection by subtracting the photocurrents from two matched photodiodes, producing a single electrical output proportional to the difference in optical power between the two inputs. This suppresses common-mode noise, such as laser intensity fluctuations, improving SNR and measurement sensitivity. Balanced Photoreceivers are engineered with a low-noise transimpedance amplifier, which ensures stable, consistent performance for precision optical measurements. Available in Si and InGaAs models for UV-VIS (320-1000nm) and NIR (800-1700nm) spectral ranges, these photoreceivers are ideal for coherent optical detection, interferometry, spectroscopy, and optical coherence tomography (OCT).

Note: Power supply sold separately. Please see specifications for more details.