

[See all 6 Products in Family](#)

## UTARGET UV Curing System



Stock **#26-821** **1 In Stock**

MRP ₹3,56,073

Price inclusive of all taxes

**ADD TO CART**

Volume Pricing	
Qty 1+	₹3,56,073 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

### Physical & Mechanical Properties

**Dimensions (mm):**

UV Curing Head: 36 Dia. x 141 Length  
Driver: 300 x 210 x 101

### Optical Properties

**Wavelength (nm):**

365.00

**Beam Diameter (mm):**

Collimated: 5 @ 5mm WD, 6 @ 25mm WD  
Focused: 3 @ 20mm WD

**Working Distance (mm):**  
5 - 45

**Irradiance (W/cm<sup>2</sup>):**  
2

## Hardware & Interface Connectivity

**Power Requirement:**  
AC 100 - 240V

## Regulatory Compliance

**Certificate of Conformance:**  
[View](#)

**Country of Origin:**  
France

**Imported By:**  
Edmund Optics India Private Limited  
267, Greystone Building, Second Floor,  
6th Cross Rd, Binnamangala,  
Stage 1, Indiranagar, Bengaluru,  
Karnataka, India 560038  
Phone: +91- 80-6845 0000

## Product Details

- Up to 5.5W/cm<sup>2</sup> UV Irradiance
- 365nm and 395nm Center Wavelengths
- Available as Wired or Wireless Devices

Handheld UV Curing LED Light Sources provide a range of output powers and beam diameters to best suit the user's application. UV curing pens #17-319 and #20-617 are wireless, handheld, and battery powered devices that provide UV irradiance up to 2W/cm<sup>2</sup> with up to 2 hours of battery life. UV curing lamps #26-821 and #12-679 are wired, handheld devices that provide adjustable UV irradiance up to 1.4W/cm<sup>2</sup> or 5.5W/cm<sup>2</sup> respectively. The wired lamps can be operated through either a button located on the handheld spot light or with an included foot pedal. Handheld UV Curing LED Light Sources are ideal for UV curing, sterilization, or fluorescence of stained gels in optical workshops and laboratories.

**Note:** Due to the high power of the UV curing lamp #12-679, we recommend using UV Protective Eyewear during operation. Speak with your health and safety manager to ensure you are selecting the proper PPE for your application.

;