

[See all 1 Products in Family](#)

UV Curing Oven



Stock #26-822 [CONTACT US](#)

⊖ 1 ⊕ MRP ₹5,41,999

● Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1+	₹5,41,999 each
Need More?	Request Quote

Product Downloads

Physical & Mechanical Properties

Weight (kg):
14

Chamber Size D x W x H (mm):
190 x 175 x 185

Dimensions (mm):
246 x 282 x 410

Optical Properties

365.00 **Wavelength (nm):**

0.25 Max **Irradiance (W/cm²):**

Hardware & Interface Connectivity

AC 100 - 305V **Power Requirement:**

Regulatory Compliance

[View](#) **Certificate of Conformance:**

France **Country of Origin:**

Imported By:
Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91-80-6845 0000

Product Details

- Up to 250mW/cm² UV Irradiance
- 365nm Center Wavelength
- Digital Control of UV Intensity and Exposure Time

The UV Curing Oven is a compact 246 x 282 x 410mm UVLED curing chamber that can provide high intensity UV irradiance up to 250mW/cm² for fast curing. Featuring a digital controller, UV light intensity can be fixed between 10% and 99% with adjustable exposure times ranging from 1 second to 100 minutes. UV reflective panels in the curing chamber provide homogeneity greater than 85% on the irradiated surface for reliable and repeatable UV emission. The UV Curing Oven is ideal for a wide range of bonding, curing, drying, hardening, and photolithography applications. A UV protection system between the lamp and the door avoids unwanted UV exposure by shutting off the UV illumination if the door is open.

FAQ(s)

? **Is the UV curing oven safe to operate?**

Yes. It features a door interlock system, 99.9% UV-blocking viewing window, and auto shut-off to prevent accidental UV exposure.

? **What are common applications of UV curing ovens?**

Typical uses include bonding, drying, hardening, photolithography, and curing specialty inks, adhesives, and coatings in research and industrial settings.