

Single Mode Optical Fiber 780-970nm, 20m



Stock **#72-893** **7 In Stock**

-

1

+

₹8,486

ADD TO CART

Volume Pricing	
Qty 1+	₹8,486 each
Need More?	Request Quote

Product Downloads

SPECIFICATIONS

General

SM

Type:

Physical & Mechanical Properties

125.0 ± 1.0

Cladding Diameter (µm):

20	Length (m):
4.4	Core Diameter (μm):
245.0 ± 15.0	Coating Diameter:
Optical Properties	
0.13	Numerical Aperture NA:
≤ 3.5 dB/km @ 850 nm ≤ 4.0 dB/km @ 780 nm	Attenuation (dB/km):
780 - 970	Wavelength Range (nm):
5.0 ± 0.5 @ 850 nm	Mode Field Diameter (nm):
Regulatory Compliance	
View	Certificate of Conformance:

PRODUCT DETAILS

- Single Mode and Polarization Maintaining Options
- 5, 10, and 20m Lengths
- Transmission Options from 450nm to 1625nm

Bare Fiber Strands are cladded step index fibers with no sheath manufactured by Coherent and Corning to allow for easy integration in space constrained systems. These fiber spools allow for direct access to the core, facilitating precise measurements and connections as well as allowing for modification to the lengths as needed. Featuring various wavelength ranges spanning the VIS and IR spectra, these fiber spools cover a wide range of applications that require specific wavelengths and provide tight cutoff tolerances. Bare Fiber Strands are designed with core diameters of 3.0μm up to 8.2μm and numerical apertures ranging from 0.12 to 0.14.