

## Single Mode Optical Fiber 980-1650nm, 10m



Stock #72-890 **2 In Stock**

- 1 + MRP ₹4,134

**i** Price inclusive of all taxes

**ADD TO CART**

Volume Pricing	
Qty 1+	₹4,134 each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

SM **Type:**

**Physical & Mechanical Properties**

125 ± 0.5 **Cladding Diameter (µm):**

10 **Length (m):**

5.3 **Core Diameter (µm):**

245.0 ± 10.0 **Coating Diameter:**

## Optical Properties

0.14 **Numerical Aperture NA:**

≤ 5.9 dB/km @ 980 nm ≤ 6.2 dB/km @ 1060 nm **Attenuation (dB/km):**

980 - 1650 **Wavelength Range (nm):**

5.9 ± 0.3 @ 980 nm  
6.2 ± 0.3 @ 1060 nm **Mode Field Diameter (nm):**

## Regulatory Compliance

[View](#) **Certificate of Conformance:**

United States **Country of Origin:**

**Imported By:**  
Edmund Optics India Private Limited  
267, Greystone Building, Second Floor,  
6th Cross Rd, Binnamangala,  
Stage 1, Indiranagar, Bengaluru,  
Karnataka, India 560038  
Phone: +91- 80-6845 0000

## Product Details

- Single Mode and Polarization Maintaining Options
- 5, 10, and 20m Lengths
- Transmission Options from 450nm to 1625nm

Bare Fiber Strands are clad step index fibers with no sheath manufactured by Coherent and Corning to allow for easy integration in space constrained systems. These fiber spools allow for direct access to the core, facilitating precise measurements and connections as well as allowing for modification to the lengths as needed. Featuring various wavelength ranges spanning the VIS and IR spectra, these fiber spools cover a wide range of applications that require specific wavelengths and provide tight cutoff tolerances. Bare Fiber Strands are designed with core diameters of 3.0µm up to 8.2µm and numerical apertures ranging from 0.12 to 0.14.